



- Products with/without grip mounting holes can be selected by the end symbol of the part number. ◀2
- **FS** ——— With grip mounting hole
- **FS-N** ——— Without grip mounting hole
- There is no grip supplied with this product. Order a grip separately.  $\rightarrow$  P.xxxx

• Material/Finish ✔ RoHS2 Compliant

	<b>FS</b>
Main body	FC200 Chrome Plating

Unit : mm

Part Number With grip mounting holes	M (Coarse)		p	Applicable recommended grip <b>SM</b> $\rightarrow$ P.xxxx	Part Number Without grip mounting holes	D <span style="color: red;">◀1</span>	H	A	s	d	C	Lc	Mass (g)
	Nominal of Thread	Pitch											
<b>FS-50</b>	M4	0.7	17	SM-4	<b>FS-40-N</b>	40	28	13	15	22	5	14.5	250
<b>FS-63</b>	M5	0.8	23	SM-5	<b>FS-50-N</b>	50	32	14	18	27	5	15	415
					<b>FS-63-N</b>	63	40	15	25	35	5	15	750

- Part number specification

**FS - 50-N**

Product Code ◀1 ◀2

Cleanroom Wash & Packaging $\rightarrow$ P.xxxx Not Available	Vibration Resistant $\rightarrow$ P.xxxx Not Available	Laser Marking $\rightarrow$ P.xxxx Not Available	Modification of Shaft Hole Diameter $\rightarrow$ P.xxxx Please feel free to contact us
--	---	---	--