



- Standard model with an aluminum disk handwheel.
- Products with/without grip mounting holes can be selected by the end symbol of the part number.

HDA — With grip mounting hole
HDA-N — Without grip mounting hole

- There is no grip supplied with this product. Order a grip separately. P.xxxx

• Material/Finish

RoHS2 Compliant

	HDA
Main body	AC8A Entire Shot Blast

Unit : mm

Part Number	M (Coarse)		P	Part Number	D	H	A	s	d	L	Mass (g)
	Nominal of Thread	Pitch									
HDA-80	M6	1	33.5	HDA-80-N	82	31	13.5	17.5	26	21	125
HDA-100	M6	1	43	HDA-100-N	103	38	14.5	23.5	28	25	200
HDA-125	M8	1.25	55	HDA-125-N	128	43	15.5	27.5	31	28	340
HDA-160	M10	1.5	70	HDA-160-N	164	51	18.5	32.5	36	32	630
HDA-200	M10	1.5	89	HDA-200-N	204	57	20.5	36.5	42	36	980

• Recommended applicable grip

Part Number	Recommended applicable grip			
	GTR P.xxxx	GNTR P.xxxx	GTM P.xxxx	HS P.xxxx
HDA-80	GTR-19 - M6	GNTR-19 - M6	GTM-19 - M6	HS-6
HDA-100	GTR-19 - M6	GNTR-19 - M6	GTM-19 - M6	HS-6
HDA-125	GTR-24 - M8	GNTR-24 - M8	GTM-24 - M8	HS-8
HDA-160	GTR-28 - M10	GNTR-28 - M10	GTM-28 - M10	HS-10
HDA-200	GTR-28 - M10	GNTR-28 - M10	GTM-28 - M10	HS-10

• Part number specification

HDA-80-N
 Product Code

Cleanroom Wash & Packaging P.xxxx	Vibration Resistant P.xxxx	Laser Marking P.xxxx	Modification of Shaft Hole Diameter P.xxxx
Available / Add'l charge	Not Available	Available / Add'l charge	Available / Add'l charge