



SPE-N(INCH) Plastic Screws - Hex Nuts - Inch Thread - PEEK NEW



Selection Tool
 CAD Download
 Chemical-proof



- Inch screw type.
- PEEK is a thermoplastic super engineering plastic superior in physical and chemical properties.
- Excellent chemical resistance. It remains almost unaffected by chemicals other than concentrated sulfuric acid, concentrated nitric acid, and concentrated hydrofluoric acid.
- With excellent heat resistance and water resistance, it retains strength at high temperatures.
- It features outstanding resistance to wear, shock, and fatigue.
- It also has high flame retardance which clears the UL 94 V-0 standard.
- Plastic screw properties and precautions for use
➔ P.xxxx

● Application

FPD production equipment / Semiconductor devices / Printed circuit board etching devices / Metallic surface treatment equipment and facilities / Chemical plants / Transformers / Electrical and electronic equipment / Hot water pumps / Chemical pumps

● Material/Finish

RoHS2 Compliant

	SPE-N(INCH)
Main Body	PEEK / Light Brown
Heat Resistance Temperature*1	260°C

* 1 : This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : inch

Part Number	# Nominal of Thread	B	T	Mass (g)	per Pack Qty
SPE-#4-40-N	No.4-40UNC	1 / 4	0.098	0.082	10
SPE-#6-32-N	No.6-32UNC	5 / 16	0.114	0.14	10
SPE-#8-32-N	No.8-32UNC	11 / 32	0.130	0.20	10

● Related Products

PEEK hex nuts **SPE-N** are available as metric threads.
➔ P.xxxx



● Part number specification

SPE-#4-40-N

Select the part number and order by number of packs. The minimum order quantity is 1 piece. ➔ P.xxxx

Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available