



- Thermosetting resin. It has a high durability.
- Types can be selected by a product code. **1**
 - PB** — Without insert
 - PC** — With insert
- There are two color variations. They can be selected by the end symbol of the part number. **4**
 - End Symbol **BK** — Black
 - End Symbol **RD** — Red

• Material/Finish



	PB	PC
Ball Part	BK : Phenol Resin (Black) RD : Melamine Resin (Red)	BK : Phenol Resin (Black) RD : Melamine Resin (Red)
Thread Part		Brass

PB Without Insert **PC** With Insert

Unit : mm

Part Number	D 2	M (Coarse)		Lf	H	Mass (g)
		Nominal of Thread 3	Pitch			
PB-20-M6	20	M6	1	10	18	5.6
PB-20-M8	20	M8	1.25	10	18	5.2
PB-25-M6	25	M6	1	10	23	11
PB-25-M8	25	M8	1.25	12	23	10
PB-30-M8	30	M8	1.25	16	28	19
PB-30-M10	30	M10	1.5	18	28	18
PB-35-M8	35	M8	1.25	16	32	31
PB-35-M10	35	M10	1.5	18	32	30
PB-40-M10	40	M10	1.5	18	37	47
PB-40-M12	40	M12	1.75	18	37	44
PC-20-M6	20	M6	1	10	18	7
PC-25-M6	25	M6	1	10	23	15
PC-25-M8	25	M8	1.25	12	23	15
PC-30-M8	30	M8	1.25	12	28	30
PC-30-M10	30	M10	1.5	15	28	30
PC-35-M8	35	M8	1.25	12	32	40
PC-35-M10	35	M10	1.5	15	32	40
PC-40-M10	40	M10	1.5	15	37	55
PC-40-M12	40	M12	1.75	15	37	50

• Part number specification



Cleanroom Wash & Packaging → P.0000	Screw Combination → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Laser Marking → P.0000
Available / Add'l charge	Not Available	Not Available	Not Available	BK only/ Add'l charge