



\* 1 : **SDSS-M8** :  $d2_{-0.1}^{-0.3}$

● Material/Finish



	<b>SDSS</b>
Main Body	Equivalent to SUS304



- The screw tip shape is a dog point.
- Use for positioning or as a rotation stopper by fitting the tip dog point shape into the counterpart groove or hole.

\* Dog point shape dimensions differ from JIS B 1177 for hex socket set screw long dog points.

## Dimensions

Unit : mm

Part Number ◀1	M (Coarse)		L1	d2	B	Mass (g)
	Nominal of Thread	Pitch				
<b>SDSS-M3</b>	M3	0.5	2.5	2.5	1.5	0.4 - 0.7
<b>SDSS-M4</b>	M4	0.7	3	3	2	0.8 - 2
<b>SDSS-M5</b>	M5	0.8	4	4	2.5	1.3 - 3.3
<b>SDSS-M6</b>	M6	1	5	4	3	1.6 - 6.3
<b>SDSS-M8</b>	M8	1.25	6.5	6	4	3.4 - 12.7

Part Number	L (mm) ◀2								
	10	12	16	20	25	30	35	40	45
<b>SDSS-M3</b>	●	●	●	●					
<b>SDSS-M4</b>		●	●	●	●	●			
<b>SDSS-M5</b>		●	●	●	●	●			
<b>SDSS-M6</b>		●	●	●	●	●	●	●	
<b>SDSS-M8</b>			●	●	●	●	●	●	●

● Part Number Specification

**SDSS-M4 - 20**



For ◀2 screw length L, select from the sizes marked with ● in the table.

Cleanroom Wash & Packaging	Screw Combination	Screw Length Adjustment	Vibration Resistant
Please feel free to contact us	Available / Add'l charge	Not Available	Available / Add'l charge