



- Set collar for securing bearings.
- It can be fixed by pressing the bearing inner wheel only on the convex of the main body.
- Optimal for securing bearing when it is difficult to fix the snap ring, etc. to the shaft.
- Clamping Type. Mounting and removing are easy. Moreover this does not scratch the shaft.
- Material/Finish ● RoHS2 Compliant

	NSCS-CB	NSCS-MB
Main body	S45C Ferrosferric Oxide Film (Black)	S45C Electroless Nickel Plating
Hex Socket Head Cap Screw	SCM435 Ferrosferric Oxide Film (Black)	SUSXM7



Part Number ◀1 Ferrosferric oxide film	Part Number 1 Electroless nickel plating	d	B	B ₁	D	D ₁	F	M(coarse)*1	Applicable bearings	Mass (g)
NSCS-3-8-CB	NSCS-3-8-MB	3	8.5	7.5	15	5	4.5	M3	693ZZ・623ZZ	9
NSCS-4-8-CB	NSCS-4-8-MB	4	8.5	7.5	15	6	4.5	M3	694ZZ・624ZZ	9
NSCS-5-8-CB	NSCS-5-8-MB	5	8.5	7.5	20	7.2	6	M3	695ZZ・605ZZ・625ZZ	15
NSCS-6-8-CB1	NSCS-6-8-MB1	6	8.5	7.5	20	9.4	6.5	M3	606ZZ	15
NSCS-6-8-CB2	NSCS-6-8-MB2	6	8.5	7.5	20	9.7	6.5	M3	626ZZ	15
NSCS-6-8-CB3	NSCS-6-8-MB3	6	8.5	7.5	20	9.1	6.5	M3	696ZZ	15
NSCS-8-8-CB1	NSCS-8-8-MB1	8	8.5	7.5	20	11.7	7	M3	608ZZ	14
NSCS-8-8-CB2	NSCS-8-8-MB2	8	8.5	7.5	20	13.2	7	M3	628ZZ	15
NSCS-8-8-CB3	NSCS-8-8-MB3	8	8.5	7.5	20	11.2	7	M3	698ZZ	15
NSCS-10-11-CB1	NSCS-10-11-MB1	10	11	9	30	14.7	9	M4	6000ZZ	41
NSCS-10-11-CB2	NSCS-10-11-MB2	10	11	9	30	17.2	9	M4	6200ZZ	42
NSCS-10-11-CB3	NSCS-10-11-MB3	10	11	9	30	14.2	9	M4	6900ZZ	42
NSCS-12-11-CB1	NSCS-12-11-MB1	12	11	9	30	17.2	10	M4	6001ZZ	39
NSCS-12-11-CB2	NSCS-12-11-MB2	12	11	9	30	18.7	10	M4	6201ZZ	41
NSCS-12-11-CB3	NSCS-12-11-MB3	12	11	9	30	16.2	10	M4	6901ZZ	41
NSCS-15-12-CB1	NSCS-15-12-MB1	15	12	11	35	20.2	12	M5	6002ZZ	58
NSCS-15-12-CB2	NSCS-15-12-MB2	15	12	11	35	21.7	12	M5	6202ZZ	59
NSCS-15-12-CB3	NSCS-15-12-MB3	15	12	11	35	19.2	12	M5	6902ZZ	58

*1: Hex socket head cap screw is provided.

Part Number ◀1 Ferrosferric oxide film	Part Number 1 Electroless nickel plating	d	B	B ₁	D	D ₁	F	M(coarse)*1	Applicable bearings	Mass (g)
NSCS-17-12-CB1	NSCS-17-12-MB1	17	12	11	35	22.2	13	M5	6003ZZ	56
NSCS-17-12-CB2	NSCS-17-12-MB2	17	12	11	35	24.2	13	M5	6203ZZ	56
NSCS-17-12-CB3	NSCS-17-12-MB3	17	12	11	35	21.2	13	M5	6903ZZ	55
NSCS-20-12-CB1	NSCS-20-12-MB1	20	12	11	40	27.2	14	M5	6004ZZ	72
NSCS-20-12-CB2	NSCS-20-12-MB2	20	12	11	40	29.2	14	M5	6204ZZ	73
NSCS-20-12-CB3	NSCS-20-12-MB3	20	12	11	40	25.2	14	M5	6904ZZ	70
NSCS-25-15-CB1	NSCS-25-15-MB1	25	15	13	45	31.7	17	M5	6005ZZ	111
NSCS-25-15-CB2	NSCS-25-15-MB2	25	15	13	45	33.2	17	M5	6205ZZ	110
NSCS-25-15-CB3	NSCS-25-15-MB3	25	15	13	45	30.2	17	M5	6905ZZ	109
NSCS-30-15-CB1	NSCS-30-15-MB1	30	15	13	55	38.2	20	M6	6006ZZ	167
NSCS-30-15-CB2	NSCS-30-15-MB2	30	15	13	55	40.2	20	M6	6206ZZ	167
NSCS-30-15-CB3	NSCS-30-15-MB3	30	15	13	55	35.2	20	M6	6906ZZ	165
NSCS-35-15-CB1	NSCS-35-15-MB1	35	15	13	60	43.2	23	M6	6007ZZ	187
NSCS-35-15-CB2	NSCS-35-15-MB2	35	15	13	60	46.2	23	M6	6207ZZ	191
NSCS-35-15-CB3	NSCS-35-15-MB3	35	15	13	60	41.2	23	M6	6907ZZ	184
NSCS-40-17-CB1	NSCS-40-17-MB1	40	17	15	70	48.2	26	M8	6008ZZ	293
NSCS-40-17-CB2	NSCS-40-17-MB2	40	17	15	70	52.2	26	M8	6208ZZ	298
NSCS-40-17-CB3	NSCS-40-17-MB3	40	17	15	70	46.2	26	M8	6908ZZ	300

*1: Hex socket head cap screw is provided.

Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Not Available	Not Available	Not Available	Available / Add'l charge

● Related Products

Set collar for stainless steel securing bearings **NSCS** is available.
→ P.xxxx



● Part number specification

NSCS-10-11-CB2

