



- Clamping type set collar.
- Installation and removing are easy. Moreover this does not scratch the shaft.
- Optimal for machines and devices that are frequently mounted/removed, e.g. slide shaft.

● Material/Finish ● RoHS2 Compliant

	NSCS-C	NSCS-M	NSCS-S
Main body	S45C Ferrosoferric Oxide Film (Black)	S45C Electroless Nickel Plating	SUS304
Hex Socket Head Cap Screw	SS400 Ferrosoferric Oxide Film (Black)	SUSXM7	SUSXM7



**NSCS-C** Made of Steel, Ferrosoferric Oxide Film    **NSCS-M** Made of Steel, Electroless Nickel Plating

**NSCS-S** Made of Stainless Steel

Part Number	Part Number	Part Number	d	B	D	F	M (coarse)*1	Mass (g)
NSCS-3-8-C	NSCS-3-8-M	NSCS-3-8-S	3	8	15	4.5	M3	9
NSCS-4-8-C	NSCS-4-8-M	NSCS-4-8-S	4	8	15	4.5	M3	9
NSCS-5-8-C	NSCS-5-8-M	NSCS-5-8-S	5	8	20	6	M3	17
NSCS-5-10-C	NSCS-5-10-M	NSCS-5-10-S	5	10	20	6	M4	21
NSCS-6-8-C	NSCS-6-8-M	NSCS-6-8-S	6	8	20	6	M3	15
NSCS-6-10-C	NSCS-6-10-M	NSCS-6-10-S	6	10	20	6	M4	20
NSCS-8-8-C	NSCS-8-8-M	NSCS-8-8-S	8	8	25	8	M3	25
NSCS-8-10-C	NSCS-8-10-M	NSCS-8-10-S	8	10	25	8	M4	31
NSCS-8-12-C	NSCS-8-12-M	NSCS-8-12-S	8	12	28	8.5	M5	49
NSCS-8-15-C	NSCS-8-15-M	NSCS-8-15-S	8	15	30	9	M6	69
NSCS-10-10-C	NSCS-10-10-M	NSCS-10-10-S	10	10	30	9	M4	44
NSCS-10-12-C	NSCS-10-12-M	NSCS-10-12-S	10	12	30	9	M5	54
NSCS-10-15-C	NSCS-10-15-M	NSCS-10-15-S	10	15	35	10	M6	93
NSCS-12-10-C	NSCS-12-10-M	NSCS-12-10-S	12	10	30	10	M4	42
NSCS-12-12-C	NSCS-12-12-M	NSCS-12-12-S	12	12	30	10	M5	51
NSCS-12-15-C	NSCS-12-15-M	NSCS-12-15-S	12	15	35	11	M6	90

\*1: Hex socket head cap screw is provided.

Part Number	Part Number	Part Number	d	B	D	F	M (coarse)*1	Mass (g)
NSCS-13-10-C	NSCS-13-10-M	NSCS-13-10-S	13	10	30	10	M4	41
NSCS-13-15-C	NSCS-13-15-M	NSCS-13-15-S	13	15	35	11	M6	88
NSCS-15-10-C	NSCS-15-10-M	NSCS-15-10-S	15	10	32	11	M4	46
NSCS-15-12-C	NSCS-15-12-M	NSCS-15-12-S	15	12	35	12	M5	68
NSCS-15-15-C	NSCS-15-15-M	NSCS-15-15-S	15	15	40	13	M6	118
NSCS-16-10-C	NSCS-16-10-M	NSCS-16-10-S	16	10	35	12	M4	54
NSCS-16-12-C	NSCS-16-12-M	NSCS-16-12-S	16	12	35	12	M5	66
NSCS-16-15-C	NSCS-16-15-M	NSCS-16-15-S	16	15	40	13	M6	114
NSCS-17-15-C	NSCS-17-15-M	NSCS-17-15-S	17	15	40	13	M6	106
NSCS-18-15-C	NSCS-18-15-M	NSCS-18-15-S	18	15	45	15	M6	143
NSCS-20-10-C	NSCS-20-10-M	NSCS-20-10-S	20	10	40	14	M4	68
NSCS-20-12-C	NSCS-20-12-M	NSCS-20-12-S	20	12	40	14	M5	81
NSCS-20-15-C	NSCS-20-15-M	NSCS-20-15-S	20	15	45	15	M6	139
NSCS-25-12-C	NSCS-25-12-M	NSCS-25-12-S	25	12	45	17	M5	96
NSCS-25-15-C	NSCS-25-15-M	NSCS-25-15-S	25	15	50	18	M6	162
NSCS-30-15-C	NSCS-30-15-M	NSCS-30-15-S	30	15	55	20	M6	183
NSCS-35-15-C	NSCS-35-15-M	NSCS-35-15-S	35	15	60	23	M6	205
NSCS-40-18-C	NSCS-40-18-M	NSCS-40-18-S	40	18	70	26	M8	347
NSCS-45-18-C	NSCS-45-18-M	NSCS-45-18-S	45	18	75	28	M8	372
NSCS-50-22-C	NSCS-50-22-M	NSCS-50-22-S	50	22	85	32	M10	603

\*1: Hex socket head cap screw is provided.

- Part number specification

**NSCS-3-8-S**



Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Please feel free to contact us	Not Available	Not Available	Available / Add'l charge