


SNPT Cross Recessed Pan Head Machine Screws - Titanium



WEB Selection Tool
 WEB CAD Download
 Cleanroom wash & packaging
 Chemical-proof
 Non-Magnetic
 Lightweight



● Physical property

	TW270 (Grade 1 Titanium)
Specific Gravity	4.51
Melting Point (°C)	1668
Longitudinal Elastic Modulus (GPa)	106
Thermal Conductivity (W / (m · K))	17.16
Linear Expansion Coefficient (K ⁻¹)	8.4 × 10 ⁻⁶
Electric Resistance (μΩ · m)	0.55
Amplitude Permeability (μ)	1.0001 (Nonmagnetic)

● Values in chart are for reference only. They are not guaranteed values.


● Mechanical property

	TW270 (Grade 1 Titanium)
Tensile Strength (N/mm ²)	270 - 410
0.2% Proof Stress (N/mm ²)	165 or Higher
Elongation (%)	27 or Higher

● Values in chart are for reference only. They are not guaranteed values.

● Part number specification

SNPT-M5-20



● Specific gravity is approximately 60% of stainless steel.

- Nonmagnetic.
- Excellent chemical and seawater resistance.
- Chemical polishing and brightening processing improve the screw surface. Furthermore, the screws are cleanroom washed, cleanroom packed, and comply with clean specifications that require no oil or foreign matter deposits.

● About the features of titanium → P.xxxx

● Application

Lightweight applications in automobiles, aircrafts, spacecrafts, and robots FPD production equipment, semiconductor devices, electrical and electronic equipment, aquatic applications, and electrochemical plating

● Material/Finish



	SNPT
Main Body	TW270 (Grade 1 Titanium)

● Related Products

SHNT Titanium Hex Nut,
SWUT Titanium Hex Lock Nut,
 and **SWAT** Titanium Washer
 are available.

→ P.xxxx



Unit : mm

Part Number 1	M (Coarse)		L 2	D1	L1	Tension*1 Rupture Load (N)	Torsional*1 Torque (N · m)	Mass (g)
	Nominal of Thread	Pitch						
SNPT-M2	M2	0.4	5 6 8 10	3.5	1.3	840	0.3	0.09 - 0.14
SNPT-M2.5	M2.5	0.45	5 6 8 10 12	4.5	1.7	1380	0.5	0.17 - 0.3
SNPT-M3	M3	0.5	6 8 10 12 16 20	5.5	2	2360	1	0.31 - 0.63
SNPT-M4	M4	0.7	6 8 10 12 16 20 25	7	2.6	4120	2.4	0.59 - 1.4
SNPT-M5	M5	0.8	8 10 12 16 20 25 30	9	3.3	6670	5.1	1.3 - 2.8

*1 : Values in chart are for reference only. They are not guaranteed values.

Part Number	Qty per pack
SNPT-M2	1
SNPT-M2.5	1
SNPT-M3	1
SNPT-M4	1
SNPT-M5	1

Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
1 unit in 1 bag	Cleanroom washed and packed	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge