


# SWAS-AWBK Adjust Metal Washer - Stainless Steel Black



WEB Selection Tool
WEB CAD Download
Antireflection
SUS Stainless steel



SWAS-AWBK



SWAS-AW

\*D=16 or less : C0.2 or less  
 D=20 or more : C0.5 or less

● Part number specification

## SWAS-5-10-3-AWBK

Product Code **1** **2** **3** Product Code

Select the t dimension from the dimension list.

- There is a variety of outside diameters and thickness relative to normal plain washers.
- For securing seating surface on the long hole position and engagement of materials with low marginal seating surface pressure such as aluminum and resin.
- As a collar and a spacer, it can adjust the cumulative error in assembly.
- Application

Height adjustment / Seating surface fall prevention

● Material/Finish

RoHS2 Compliant

	<b>SWAS-AWBK</b>
Main body	SUS304 Stainless Steel Black

Unit : mm

Part Number	d <b>1</b>	D <b>2</b>	t <b>3</b>					Mass (g)	Qty per pack
			1	1.5	2	3	5		
SWAS-3-8-AWBK	3	8	●		●			0.35 - 0.69	1
SWAS-4-8-AWBK	4	8	●	●	●			0.3 - 0.6	1
SWAS-4-10-AWBK	4	10	●		●	●		0.53 - 1.6	1
SWAS-4-12-AWBK	4	12	●		●	●		0.8 - 2.4	1
SWAS-5-8-AWBK	5	8	●	●	●			0.25 - 0.49	1
SWAS-5-10-AWBK	5	10	●		●	●		0.47 - 1.4	1
SWAS-5-12-AWBK	5	12	●		●	●		0.74 - 2.2	1
SWAS-5-16-AWBK	5	16			●	●		2.9 - 4.3	1
SWAS-5-20-AWBK	5	20	●		●			2.3 - 4.7	1
SWAS-6-10-AWBK	6	10	●		●	●		0.4 - 1.2	1
SWAS-6-12-AWBK	6	12	●		●	●		0.68 - 2	1
SWAS-6-16-AWBK	6	16			●	●	●	2.7 - 6.8	1
SWAS-6-20-AWBK	6	20	●		●	●	●	2.3 - 11	1
SWAS-6-25-AWBK	6	25			●	●	●	7.3 - 18	1
SWAS-8-12-AWBK	8	12			●	●	●	1 - 2.5	1
SWAS-8-16-AWBK	8	16			●	●	●	2.4 - 6	1
SWAS-8-20-AWBK	8	20			●	●	●	4.2 - 10	1
SWAS-8-25-AWBK	8	25			●	●	●	7 - 17	1
SWAS-10-12-AWBK	10	12			●	●	●	0.55 - 1.4	1
SWAS-10-16-AWBK	10	16				●	●	2.9 - 4.8	1
SWAS-10-20-AWBK	10	20			●	●	●	3.7 - 9.3	1
SWAS-10-25-AWBK	10	25				●	●	9.8 - 16	1
SWAS-12-16-AWBK	12	16				●	●	2.1 - 3.5	1
SWAS-12-20-AWBK	12	20			●	●	●	3.2 - 8	1
SWAS-12-25-AWBK	12	25				●	●	9 - 15	1
SWAS-16-25-AWBK	16	25				●	●	6.9 - 11	1

Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
1 pc. in 1 bag	Available / Add'l charge	Not Available	Not Available	Not Available