



- Split-type set collar.
- As the axial hole part can be completely split, so mounting and removing can be performed easily. Moreover this does not scratch the shaft.
- Optimal for use with machines and devices that are difficult to disassemble.

• Material/Finish ● RoHS2 Compliant

	NSCSS-C	NSCSS-M	NSCSS-S
Main body	S45C Ferrosoferric Oxide Film (Black)	S45C Electroless Nickel Plating	SUS304
Hex Socket Head Cap Screw	SCM435 Ferrosoferric Oxide Film (Black)	SUSXM7	SUSXM7



NCS55-C Made of Steel, Ferrosoferric Oxide Film
 NCS55-M Made of Steel, Electroless Nickel Plating
 NCS55-S Made of Stainless Steel

Unit : mm

Part Number	Part Number	Part Number	d	B	D	F	M (coarse) *1	Mass (g)
NCS55-3-8-C	NCS55-3-8-M	NCS55-3-8-S	3	8	15	4.5	M3	9
NCS55-4-8-C	NCS55-4-8-M	NCS55-4-8-S	4	8	15	4.5	M3	7
NCS55-5-8-C	NCS55-5-8-M	NCS55-5-8-S	5	8	20	5.5	M3	14
NCS55-5-10-C	NCS55-5-10-M	NCS55-5-10-S	5	10	20	6	M4	20
NCS55-6-8-C	NCS55-6-8-M	NCS55-6-8-S	6	8	20	6	M3	15
NCS55-6-10-C	NCS55-6-10-M	NCS55-6-10-S	6	10	20	6	M4	19
NCS55-8-8-C	NCS55-8-8-M	NCS55-8-8-S	8	8	25	8	M3	24
NCS55-8-10-C	NCS55-8-10-M	NCS55-8-10-S	8	10	25	8	M4	30
NCS55-8-12-C	NCS55-8-12-M	NCS55-8-12-S	8	12	28	8.5	M5	47
NCS55-8-15-C	NCS55-8-15-M	NCS55-8-15-S	8	15	30	9	M6	63
NCS55-10-10-C	NCS55-10-10-M	NCS55-10-10-S	10	10	30	9	M4	41
NCS55-10-12-C	NCS55-10-12-M	NCS55-10-12-S	10	12	30	9	M5	51
NCS55-10-15-C	NCS55-10-15-M	NCS55-10-15-S	10	15	35	10	M6	86
NCS55-12-10-C	NCS55-12-10-M	NCS55-12-10-S	12	10	30	10	M4	40
NCS55-12-12-C	NCS55-12-12-M	NCS55-12-12-S	12	12	30	10	M5	49
NCS55-12-15-C	NCS55-12-15-M	NCS55-12-15-S	12	15	35	11	M6	84
NCS55-13-10-C	NCS55-13-10-M	NCS55-13-10-S	13	10	30	10	M4	38
NCS55-13-15-C	NCS55-13-15-M	NCS55-13-15-S	13	15	35	11	M6	80

*1 : Hex socket head cap screw is provided.

Unit : mm

Part Number	Part Number	Part Number	d	B	D	F	M (coarse) *1	Mass (g)
NCS55-15-10-C	NCS55-15-10-M	NCS55-15-10-S	15	10	32	11	M4	42
NCS55-15-12-C	NCS55-15-12-M	NCS55-15-12-S	15	12	35	12	M5	64
NCS55-15-15-C	NCS55-15-15-M	NCS55-15-15-S	15	15	40	13	M6	109
NCS55-16-10-C	NCS55-16-10-M	NCS55-16-10-S	16	10	35	12	M4	51
NCS55-16-12-C	NCS55-16-12-M	NCS55-16-12-S	16	12	35	12	M5	62
NCS55-16-15-C	NCS55-16-15-M	NCS55-16-15-S	16	15	40	13	M6	107
NCS55-17-15-C	NCS55-17-15-M	NCS55-17-15-S	17	15	40	13	M6	106
NCS55-18-15-C	NCS55-18-15-M	NCS55-18-15-S	18	15	45	15	M6	136
NCS55-20-10-C	NCS55-20-10-M	NCS55-20-10-S	20	10	40	14	M4	65
NCS55-20-12-C	NCS55-20-12-M	NCS55-20-12-S	20	12	40	14	M5	77
NCS55-20-15-C	NCS55-20-15-M	NCS55-20-15-S	20	15	45	15	M6	131
NCS55-25-12-C	NCS55-25-12-M	NCS55-25-12-S	25	12	45	17	M5	92
NCS55-25-15-C	NCS55-25-15-M	NCS55-25-15-S	25	15	50	18	M6	152
NCS55-30-15-C	NCS55-30-15-M	NCS55-30-15-S	30	15	55	20	M6	171
NCS55-35-15-C	NCS55-35-15-M	NCS55-35-15-S	35	15	60	23	M6	195
NCS55-40-18-C	NCS55-40-18-M	NCS55-40-18-S	40	18	70	26	M8	334
NCS55-45-18-C	NCS55-45-18-M	NCS55-45-18-S	45	18	75	28	M8	356
NCS55-50-22-C	NCS55-50-22-M	NCS55-50-22-S	50	22	85	32	M10	576

*1 : Hex socket head cap screw is provided.

- Part number specification

NCS55-10-15-C



Cleanroom Wash & Packaging → P. xxxx	Screw Length Adjustment → P. xxxx	Vibration Resistant → P. xxxx	Laser Marking → P. xxxx
Please feel free to contact us	Not Available	Not Available	Available / Add'l charge