



- 材質・仕上げ



	KEHS-K-HP
本体	SUS303相当 研磨



- 耐蝕性にすぐれたステンレス製のノブ。
- 表面は研磨仕上げ。
- めねじ・貫通穴タイプ。

単位：mm

品番 	D	M(並目)		Lf	H	s	d	質量(g)
		ねじの呼び	ピッチ					
KEHS-40-K6-HP	40	M6	1	13	30.5	15	18	132
KEHS-40-K8-HP	40	M8	1.25	13	30.5	15	18	125
KEHS-50-K8-HP	50	M8	1.25	16	34	17	21	225
KEHS-50-K10-HP	50	M10	1.5	16	34	17	21	202
KEHS-60-K10-HP	60	M10	1.5	20	39	18	25	360
KEHS-60-K12-HP	60	M12	1.75	20	39	18	25	348

- 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

KEHS-50-K8-HP



 クリーン洗浄・クリーン梱包 お問い合わせください	 ねじ組み合わせ 対応可・別料金	 ねじカット 対応不可	 ゆるみ止め 対応不可	 レーザ刻印 対応可・別料金
---	--	---	---	--