



- 取り付け用のねじを組み込んだゴム製バンパ。装置・機械への取り付けが容易です。
- 片側おねじタイプ。
- ゴムは環境に配慮したNR(天然ゴム)を使用。
- 衝撃吸収・振動吸収などの用途のほか、装置・機械の足としても使用できます。
- ねじ部の材質は2種類。商品記号により選択できます。

FGBA ——— スティール製
FGBAS ——— ステンレス製

FGBA-S ねじ部：スティール製

品番	価格(円)	D	H	M(並目)		Lm	t	ばね定数(N/mm)	最大荷重(N)	最大たわみ量	質量(g)
				ねじの呼び	ピッチ						
FGBA-8-8-M3-S-55	140	8	8	M3	0.5	6	1	20	40	2	2
FGBA-10-10-M4-S-55	130	10	10	M4	0.7	10	1.2	24	59	2.5	4
FGBA-10-15-M4-S-55	130	10	15	M4	0.7	10	1.2	21	78	3.75	5
FGBA-15-10-M4-S-55	130	15	10	M4	0.7	10	1.4	77	154	2	7
FGBA-15-15-M4-S-55	130	15	15	M4	0.7	10	1.4	64	241	3.75	8
FGBA-15-20-M4-S-55	140	15	20	M4	0.7	10	1.4	57	287	5	9
FGBA-15-30-M4-S-55	160	15	30	M4	0.7	10	1.4	48	300	6.25	10
FGBA-20-10-M6-S-55	140	20	10	M6	1	18	2	126	315	2.5	12
FGBA-20-15-M6-S-55	140	20	15	M6	1	18	2	77	289	3.75	14
FGBA-20-20-M6-S-55	150	20	20	M6	1	18	2	60	302	5	16
FGBA-20-30-M6-S-55	170	20	30	M6	1	18	2	38	285	7.5	20
FGBA-25-15-M6-S-55	160	25	15	M6	1	18	2	163	612	3.75	22
FGBA-25-20-M6-S-55	180	25	20	M6	1	18	2	112	560	5	25
FGBA-25-30-M6-S-55	210	25	30	M6	1	18	2	68	509	7.5	31
FGBA-30-15-M8-S-55	230	30	15	M8	1.25	20	2	249	934	3.75	43
FGBA-30-20-M8-S-55	260	30	20	M8	1.25	20	2	185	924	5	47
FGBA-30-25-M8-S-55	280	30	25	M8	1.25	20	2	130	815	6.25	51
FGBA-30-30-M8-S-55	290	30	30	M8	1.25	20	2	117	876	7.5	55
FGBA-40-20-M8-S-55	330	40	20	M8	1.25	23	2	247	1235	5	62
FGBA-40-25-M8-S-55	380	40	25	M8	1.25	23	2	247	1546	6.25	74
FGBA-40-30-M8-S-55	400	40	30	M8	1.25	23	2	213	1600	7.5	85
FGBA-40-40-M8-S-55	480	40	40	M8	1.25	23	2	182	1820	10	108
FGBA-50-20-M10-S-55	500	50	20	M10	1.5	28	2	517	2587	5	127
FGBA-50-30-M10-S-55	570	50	30	M10	1.5	28	2	327	2453	7.5	150
FGBA-50-40-M10-S-55	670	50	40	M10	1.5	28	2	247	2468	10	173
FGBA-60-20-M10-S-55	(900)	60	20	M10	1.5	28	2	726	3630	5	171
FGBA-60-40-M10-S-55	(1,120)	60	40	M10	1.5	28	2	340	3400	10	233
FGBA-70-40-M10-S-55	(1,710)	70	40	M10	1.5	27	3	410	4100	10	291
FGBA-70-55-M10-S-55	(2,000)	70	55	M10	1.5	27	3	327	4500	13.75	348
FGBA-75-25-M12-S-55	(1,250)	75	25	M12	1.75	37	3	752	4700	6.25	233
FGBA-75-40-M12-S-55	(1,490)	75	40	M12	1.75	37	3	450	4500	10	349
FGBA-75-50-M12-S-55	(1,740)	75	50	M12	1.75	37	3	352	4400	12.5	426
FGBA-100-40-M16-S-55	(3,240)	100	40	M16	2	41	3	810	8100	10	638
FGBA-100-50-M16-S-55	(3,600)	100	50	M16	2	41	3	640	8000	12.5	828
FGBA-100-60-M16-S-55	(3,790)	100	60	M16	2	41	3	520	7800	15	1008

● 価格が()の商品は非在庫品です。実働10日目出荷になります。

● 材質・仕上げ



	FGBA-S	FGBAS-S
本体	NR(天然ゴム) 硬度ショアA55±5	NR(天然ゴム) 硬度ショアA55±5
ねじ部	スティール 三価クロメート処理	ステンレス
カバーシート	スティール 三価クロメート処理	ステンレス



FGBAS-S ねじ部：ステンレス製

品番	価格(円)	D	H	M(並目)		Lm	t	ばね定数(N/mm)	最大荷重(N)	最大たわみ量	質量(g)
				ねじの呼び	ピッチ						
FGBAS-8-8-M3-S-55	400	8	8	M3	0.5	6	1	20	40	2	2
FGBAS-10-10-M4-S-55	330	10	10	M4	0.7	10	1.2	24	59	2.5	4
FGBAS-10-15-M4-S-55	340	10	15	M4	0.7	10	1.2	21	78	3.75	5
FGBAS-15-10-M4-S-55	330	15	10	M4	0.7	10	1.4	77	154	2	7
FGBAS-15-15-M4-S-55	340	15	15	M4	0.7	10	1.4	64	241	3.75	8
FGBAS-15-20-M4-S-55	360	15	20	M4	0.7	10	1.4	57	287	5	9
FGBAS-15-30-M4-S-55	420	15	30	M4	0.7	10	1.4	48	300	6.25	10
FGBAS-20-10-M6-S-55	380	20	10	M6	1	18	2	126	315	2.5	12
FGBAS-20-15-M6-S-55	400	20	15	M6	1	18	2	77	289	3.75	14
FGBAS-20-20-M6-S-55	410	20	20	M6	1	18	2	60	302	5	16
FGBAS-20-30-M6-S-55	460	20	30	M6	1	18	2	38	285	7.5	20
FGBAS-25-15-M6-S-55	480	25	15	M6	1	18	2	163	612	3.75	22
FGBAS-25-20-M6-S-55	530	25	20	M6	1	18	2	112	560	5	25
FGBAS-25-30-M6-S-55	630	25	30	M6	1	18	2	68	509	7.5	31
FGBAS-30-15-M8-S-55	700	30	15	M8	1.25	20	2	249	934	3.75	43
FGBAS-30-20-M8-S-55	750	30	20	M8	1.25	20	2	185	924	5	47
FGBAS-30-25-M8-S-55	830	30	25	M8	1.25	20	2	130	815	6.25	51
FGBAS-30-30-M8-S-55	890	30	30	M8	1.25	20	2	117	876	7.5	55
FGBAS-40-20-M8-S-55	1,010	40	20	M8	1.25	23	2	247	1235	5	62
FGBAS-40-25-M8-S-55	1,130	40	25	M8	1.25	23	2	247	1546	6.25	74
FGBAS-40-30-M8-S-55	1,200	40	30	M8	1.25	23	2	213	1600	7.5	85
FGBAS-40-40-M8-S-55	1,410	40	40	M8	1.25	23	2	182	1820	10	108
FGBAS-50-20-M10-S-55	1,410	50	20	M10	1.5	28	2	517	2587	5	127
FGBAS-50-30-M10-S-55	1,690	50	30	M10	1.5	28	2	327	2453	7.5	150
FGBAS-50-40-M10-S-55	1,980	50	40	M10	1.5	28	2	247	2468	10	173
FGBAS-60-20-M10-S-55	(2,450)	60	20	M10	1.5	28	2	726	3630	5	171
FGBAS-60-40-M10-S-55	(3,070)	60	40	M10	1.5	28	2	340	3400	10	233
FGBAS-70-40-M10-S-55	(4,700)	70	40	M10	1.5	27	3	410	4100	10	291
FGBAS-70-55-M10-S-55	(5,500)	70	55	M10	1.5	27	3	327	4500	13.75	348
FGBAS-75-25-M12-S-55	(3,450)	75	25	M12	1.75	37	3	752	4700	6.25	233
FGBAS-75-40-M12-S-55	(4,100)	75	40	M12	1.75	37	3	450	4500	10	349
FGBAS-75-50-M12-S-55	(4,790)	75	50	M12	1.75	37	3	352	4400	12.5	426
FGBAS-100-40-M16-S-55	(8,940)	100	40	M16	2	41	3	810	8100	10	638
FGBAS-100-50-M16-S-55	(9,910)	100	50	M16	2	41	3	640	8000	12.5	828
FGBAS-100-60-M16-S-55	(10,400)	100	60	M16	2	41	3	520	7800	15	1008

● 価格が()の商品は非在庫品です。実働10日目出荷になります。

● 品番指定 直送 14時当日出荷 NBK ネットショップ

FGBA-30-30-M8-S-55

1
 価格が()の商品は非在庫品です。実働10日目出荷になります。

クリーン洗浄・クリーン梱包 → P.0000	ねじカット → P.0000	ゆるみ止め → P.0000	レーザ刻印 → P.0000
対応不可	対応不可	対応可・別料金	対応不可