




- 位置決め、治具固定用の精密ボルト。

- 材質・仕上げ

 RoHS2適合

	SBM
本体	SUM22L、浸炭窒化(硬度550 - 650HV)・研削 四三酸化鉄皮膜(黒)

単位: mm

品番	価格(円)	M(並目) 	D <sub>2</sub> 	L <sub>2</sub> 	D	L <sub>3</sub>	L <sub>1</sub> (約)	L	質量(g)
SBM-M5-6-5	640	M5	6 <sup>-0.03</sup> <sub>-0.05</sub>	5	12	15	3	7	4
SBM-M5-6-6	680	M5	6 <sup>-0.03</sup> <sub>-0.05</sub>	6	12	16	3	7	4
SBM-M5-6-7	700	M5	6 <sup>-0.03</sup> <sub>-0.05</sub>	7	12	17	3	7	5
SBM-M5-6-8	740	M5	6 <sup>-0.03</sup> <sub>-0.05</sub>	8	12	18	3	7	5
SBM-M6-8-5	530	M6	8 <sup>-0.05</sup> <sub>-0.08</sub>	5	14	17	4	8	8
SBM-M6-8-6	530	M6	8 <sup>-0.05</sup> <sub>-0.08</sub>	6	14	18	4	8	8
SBM-M6-8-8	570	M6	8 <sup>-0.05</sup> <sub>-0.08</sub>	8	14	20	4	8	9
SBM-M6-8-9	570	M6	8 <sup>-0.05</sup> <sub>-0.08</sub>	9	14	21	4	8	9
SBM-M6-8-10	570	M6	8 <sup>-0.05</sup> <sub>-0.08</sub>	10	14	22	4	8	10
SBM-M6-8-12	720	M6	8 <sup>-0.05</sup> <sub>-0.08</sub>	12	14	24	4	8	10
SBM-M6-8-13	750	M6	8 <sup>-0.05</sup> <sub>-0.08</sub>	13	14	25	4	8	11
SBM-M8-10-8	650	M8	10 <sup>-0.05</sup> <sub>-0.08</sub>	8	16	24	5	11	16
SBM-M8-10-10	640	M8	10 <sup>-0.05</sup> <sub>-0.08</sub>	10	16	26	5	11	17
SBM-M8-10-12	680	M8	10 <sup>-0.05</sup> <sub>-0.08</sub>	12	16	28	5	11	18
SBM-M8-10-14	730	M8	10 <sup>-0.05</sup> <sub>-0.08</sub>	14	16	30	5	11	19
SBM-M8-10-15	750	M8	10 <sup>-0.05</sup> <sub>-0.08</sub>	15	16	31	5	11	19
SBM-M10-12-12	750	M10	12 <sup>-0.05</sup> <sub>-0.08</sub>	12	19	31	6	13	29
SBM-M10-12-14	760	M10	12 <sup>-0.05</sup> <sub>-0.08</sub>	14	19	33	6	13	30
SBM-M10-12-16	780	M10	12 <sup>-0.05</sup> <sub>-0.08</sub>	16	19	35	6	13	31
SBM-M10-12-17	980	M10	12 <sup>-0.05</sup> <sub>-0.08</sub>	17	19	36	6	13	32
SBM-M12-14-14	1,580	M12	14 <sup>-0.05</sup> <sub>-0.08</sub>	14	22	38	8	16	49
SBM-M12-14-16	1,580	M12	14 <sup>-0.05</sup> <sub>-0.08</sub>	16	22	40	8	16	51
SBM-M12-14-18	1,660	M12	14 <sup>-0.05</sup> <sub>-0.08</sub>	18	22	42	8	16	53

- 品番指定



SBM-M10-12-16

商品  
記号

クリーン洗浄・クリーン梱包 → P. xxxx

対応不可

ねじ組み合わせ → P. xxxx

対応不可

ねじカット → P. xxxx

対応不可

ゆるみ止め → P. xxxx

対応可・別料金