



- 耐久性にすぐれたフェノール樹脂製。
- 力のかかりやすい形状です。

● 材質・仕上げ



KJF-PF	
ノブ	フェノール樹脂(黒)
ねじ部	スチール 三価クロメート処理

単位: mm

品番 	D	M(並目)		Lf min.	H	s	d	質量(g)
		ねじの呼び	ピッチ					
KJF-25-M5-PF	25	M5	0.8	9.5	17	8	13	7
KJF-32-M6-PF	32	M6	1	12	20	10	14	10
KJF-40-M8-PF	40	M8	1.25	14	25	13	18	20
KJF-50-M10-PF	50	M10	1.5	18	32	20	22	32
KJF-63-M12-PF	63	M12	1.75	22	40	25	26	55
KJF-80-M16-PF	80	M16	2	30	50	30	35	111
KJF-100-M20-PF	100	M20	2.5	30	65	38	34	211

- 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

KJF-32-M6-PF



 クリーン洗浄・クリーン梱包 対応不可	 ねじ組み合わせ お問い合わせください	 ねじカット 対応不可	 ゆるみ止め 対応不可	 レーザ刻印 対応可・別料金
---	---	---	---	--