




SWAS-AWBK

Adjust Metal Washer - Stainless Steel Black

Chemical-proof Antireflection SUS Stainless steel



*D=16 or less : C0.2 or less
D=20 or more : C0.5 or less

Part number specification

SWAS-5-10-3-AWBK

Product Code 1 2 3 Product Code

For 3 t dimension, select from the sizes marked with ● in the table.

SWAS-AWBK



SWAS-AW

- There is a variety of outside diameters and thickness relative to normal plain washers.
- For securing seating surface on the long hole position and engagement of materials with low marginal seating surface pressure such as aluminum and resin.
- As a collar and a spacer, it can adjust the cumulative error in assembly.
- Application

Height adjustment / Seating surface fall prevention

Material/Finish



	SWAS-AWBK
Main body	SUS304 Stainless Steel Black

Unit : mm

Part Number	d 1	D 2	t 3					Mass (g)
			1	1.5	2	3	5	
SWAS-3-8-AWBK	3	8	●		●			0.35 - 0.69
SWAS-4-8-AWBK	4	8	●	●	●			0.3 - 0.6
SWAS-4-10-AWBK	4	10	●		●	●		0.53 - 1.6
SWAS-4-12-AWBK	4	12	●		●	●		0.8 - 2.4
SWAS-5-8-AWBK	5	8	●	●	●			0.25 - 0.49
SWAS-5-10-AWBK	5	10	●		●	●		0.47 - 1.4
SWAS-5-12-AWBK	5	12	●		●	●		0.74 - 2.2
SWAS-5-16-AWBK	5	16			●	●		2.9 - 4.3
SWAS-5-20-AWBK	5	20	●		●			2.3 - 4.7
SWAS-6-10-AWBK	6	10	●		●	●		0.4 - 1.2
SWAS-6-12-AWBK	6	12	●		●	●		0.68 - 2
SWAS-6-16-AWBK	6	16			●	●	●	2.7 - 6.8
SWAS-6-20-AWBK	6	20	●		●	●	●	2.3 - 11
SWAS-6-25-AWBK	6	25			●	●	●	7.3 - 18
SWAS-8-12-AWBK	8	12			●	●	●	1 - 2.5
SWAS-8-16-AWBK	8	16			●	●	●	2.4 - 6
SWAS-8-20-AWBK	8	20			●	●	●	4.2 - 10
SWAS-8-25-AWBK	8	25			●	●	●	7 - 17
SWAS-10-12-AWBK	10	12			●	●	●	0.55 - 1.4
SWAS-10-16-AWBK	10	16				●	●	2.9 - 4.8
SWAS-10-20-AWBK	10	20			●	●	●	3.7 - 9.3
SWAS-10-25-AWBK	10	25				●	●	9.8 - 16
SWAS-12-16-AWBK	12	16				●	●	2.1 - 3.5
SWAS-12-20-AWBK	12	20			●	●	●	3.2 - 8
SWAS-12-25-AWBK	12	25				●	●	9 - 15
SWAS-16-25-AWBK	16	25				●	●	6.9 - 11

1 Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
1 piece in 1 pack	Available / Add'l charge	Not Available	Not Available	Not Available