


DTT Tablet PC Holders - for iPad - 360°Rotation Type - Spring Retention

[WEB Selection Tool](#)
[WEB CAD Download](#)
[Aluminum frame mount](#)
[wall/panel Mount](#)
[Aluminum frame edge mount](#)
[Pipe](#)

Structure



Material/Finish

	DTT-AF	DTT-AA / DTT-PB
Holder	SS400 Chrome Plating	
Protection Cap	Flexible PVC (lead-free)	
Ball Case	A6063 Anodized	
Ball	S45C Trivalent Chromate Treatment	
Built-in Spring	Spring Steel	
Fixing Plate	SS400 Electrostatic Coating	—
Bracket	—	A6063 Anodized

Retention torque

Product Code	Retention Torque	Reference Force
DTTH	20 N・m	Even in an environment subject to vibration, etc., the tablet PC is unlikely to deviate.
DTTM	15 N・m	Middle of low torque type and high torque type.
DTTL	10 N・m	Can move with torque equivalent to that for household / office PC displays.

Option

- By using the optional **[DTC]**, a tablet PC can be completely fixed.
- For cases where the mounting direction must be changed or taking out the tablet PC is prohibited.

Part Number	Mass (g)
DTC	70

Material / Finish




	DTC
Clamp	AC4C-F Electrostatic Coating
Clamping Screw	SUSXM7


Related Products

A 360° rotation type tablet PC mounting system **[DTK]** that tightens the fixing bolts to retain the angle is available.

➔ P.xxxx



- Tablet PC holder compatible with iPad*1.
*1: iPad is a trademark of Apple Inc. Compatible with iPad2, iPad3, and iPad4.
- This fixes a tablet PC to production equipment or test devices. Tablet PC can be mounted / unmounted easily just by inserting / removing it.
- Robust design. It has excellent durability.
- The built-in spring serves to retain the angle. Tightening after adjustment is not necessary.
- Three types of Mounting System for Display® are available for different types of mounting surfaces. 
 - For aluminum frame / For wall panel and sheet metal—**[DTT-AF]**
 - For aluminum frame end surface mounting—**[DTT-AA]**
 - For Round Pipe—**[DTT-PB]**
- This is suitable for checking the tablet PC screen while both hands are in use.
- For detailed dimensions of the holder, refer to **[DTR]**. ➔ P.xxxx
- The holder can be tilted by $\pm 15^\circ$ to any direction. It can also be rotated by 360° .



- We also produce Mounting System for Display® with special specifications compatible with tablet PCs of various sizes.

➔ P.xxxx



Application

Machine tool / Medical equipment / FPD production device / Semiconductor manufacturing device / Packing machine / Food machinery

Part number specification

DTT M-AA-40

Product Code   

Example of part number: DTTL-AF-M8 / DTTH-PB-40

- For aluminum frame / For wall panel and sheet metal

[DTT-AF]



Part Number	M*1 (d)	Mass (g)
DTT*-AF-**	M4 (5)	1860
	M5 (6)	
	M6 (7)	
	M8 (9)	

*1: Mounting bolts are not supplied.

- For aluminum frame end surface mounting

[DTT-AA]



Part Number	B	Mass (g)
DTT*-AA-40	40	1630

*1: Hex socket low head bolts (M8 × 16 mm) are provided.

- For Round Pipe

[DTT-PB]



Part Number	D	L ₁	L	Mass (g)
DTT*-PB-**	28	120.5	144.5	1780
	30			1780
	34			1770
	40	124.5	152.5	1760
	42.7			1760

- Fixing rubber sheet is attached. Dimensional allowance of available round pipe is ± 0.5 mm.

