


SLT/SLTS Hexalobular Socket Head Cap Screws with Low Profile

WEB Selection Tool | WEB CAD Download | SUS Stainless steel | Protrusion



Application

Reducing the size of equipment and devices

Material/Finish

RoHS2 Compliant

	SLT-TZB	SLTS
Main Body	SAE1022 Trivalent Chromate Treatment	SUSXM7 (Equivalent to SUS304)
Strength Class	8.8	A2-50

- Hexalobular socket*1 head cap screws with low head height.
- For space-saving of equipment/devices and applications with limited overhead space.
- Hexalobular socket shapes*1 are designed to withstand high tightening torque. → P.xxxx
- Install and remove with **SKX** Dedicated Wrench or **SKXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- Use the **SKX-N** hexalobular wrench for extremely limited access spaces for mounting and removing in tight spaces.

*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

Unit : mm

SLT-TZB Steel - Trivalent Chromate Treatment	SLTS Stainless steel	Common dimensions																			
Part Number	Part Number	M (Coarse)		L								D1	L1	Applicable wrench	Hexalobular Socket No.	t	Mass (g)				
		Nominal of Thread	Pitch	4	5	6	8	10	12	16	20							25	30		
	SLTS-M2	M2	0.4	4	5	6	8	10					3.8	1.55	SKX-6	6	0.84	0.11 - 0.23			
	SLTS-M2.5	M2.5	0.45		5	6	8	10	12				4.5	1.85	SKX-8	8	0.91	0.26 - 0.47			
SLT-M3-TZB	SLTS-M3	M3	0.5			6	8	10	12	16			5.5	2.4	SKX-10	10	1.27	0.53 - 0.98			
SLT-M4-TZB	SLTS-M4	M4	0.7				6	8	10	12	16	20	7	3.1	SKX-20	20	1.66	1.1 - 2.3			
SLT-M5-TZB	SLTS-M5	M5	0.8					8	10	12	16	20	25	8.5	3.65	SKX-25	25	1.91	1.8 - 4.1		
SLT-M6-TZB	SLTS-M6	M6	1						8	10	12	16	20	25	30	10	4.4	SKX-30	30	2.29	3.1 - 7.1

SLT-TZB Steel - Trivalent Chromate Treatment

Part Number	Qty*1 per pack
SLT-M3-TZB	50
SLT-M4-TZB	50
SLT-M5-TZB	50
SLT-M6-TZB	20

*1: Also sold separately from 1 piece up. → P.xxxx

SLTS Stainless Steel

Part Number	Qty*1 per pack
SLTS-M2	50
SLTS-M2.5	50
SLTS-M3	50
SLTS-M4	50
SLTS-M5	50
SLTS-M6	20

*1: Also sold separately from 1 piece up. → P.xxxx

Individual Sales → P.xxxx | Cleanroom Wash & Packaging → P.xxxx | Screw Length Adjustment → P.xxxx | Vibration Resistant → P.xxxx | Modification process for captive use → P.xxxx
 Available / Add'l charge | Available / Add'l charge | Available / Add'l charge | Available / Add'l charge | Please feel free to contact us

Related Products

SKX Hexalobular Wrench
→ P.xxxx



SKX-N Hexalobular Wrench for Extremely Limited Access Spaces
→ P.xxxx



SKXB Hexalobular Short Bit
→ P.xxxx



SRD Magnet Screwdriver
→ P.xxxx



Part number specification

SLT-M5-20-TZB
1 2 3 1

Order in number of packs.
Also sold separately from 1 piece up. → P.xxxx