




SNPXS Hexalobular Socket Pan Head Machine Screws

SUS Stainless steel Protrusion



● Application

Prevention of damage to screw heads and reliable tightening

● Material/Finish



	SNPXS
Material	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50

● Part number specification

SNPXS-M5 - 20



- Hexalobular socket shapes*1 are designed to withstand high tightening torque compared to cross-recesses.
- Screw heads are unlikely to be damaged due to tightening, allowing safe and secure tightening to be performed.
- Mounting/removing with regular tools such as hex keys and screwdrivers is not possible. Also usable for applications including prevention of disassembly, theft, or tampering for devices or facilities.* 2
- Install and remove with **SKX** Dedicated Wrench or **SKXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- Use the **SKX-N** hexalobular wrench for extremely limited access spaces for mounting and removing in tight spaces.
- Conforms to ISO 14583.

*1: The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

*2: Tools for hexalobular sockets are commercially available. When tampering prevention is the main objective, consider tamper resistant screws. ➔ P.xxxx

Unit : mm

Part Number	M (Coarse)		L										D1	L1	Applicable wrench	Hexalobular Socket No.	t	Mass (g)	Qty per pack
	Nominal of Thread	Pitch	4	5	6	8	10	12	16	20	25	30							
SNPXS-M2	M2	0.4	4	5	6	8	10	12					4	1.6	SKX-6	6	0.77	0.14 - 0.29	20
SNPXS-M2.5	M2.5	0.45	4	5	6	8	10	12	16				5	2.1	SKX-8	8	1.04	0.27 - 0.65	20
SNPXS-M3	M3	0.5		5	6	8	10	12	16	20			5.6	2.4	SKX-10	10	1.27	0.49 - 1.1	20
SNPXS-M4	M4	0.7			6	8	10	12	16	20	25		8	3.1	SKX-20	20	1.66	1 - 2.5	20
SNPXS-M5	M5	0.8				8	10	12	16	20	25	30	9.5	3.7	SKX-25	25	1.91	2.2 - 4.8	20
SNPXS-M6	M6	1					10	12	16	20	25	30	12	4.6	SKX-30	30	2.42	3.9 - 7.4	20

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Related Products

SKX Hexalobular Wrench



SKXB Hexalobular Short Bit



SKX-N Hexalobular Wrench for Extremely Limited Access Spaces



SRD Magnet Screwdriver



Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge