


SKXB Hexalobular Short Bits **NEW**

WEB Selection Tool



● Material/Finish

	SKXB
Main Body	Tool Steel (Hardness: 60HRC or Higher)

- Short bit dedicated for hexalobular screws.
- Use in combination with the dedicated magnetic screwdriver **SRD** and commercial bit-interchangeable screwdrivers.
- Torque management of hexalobular screws is possible by use in combination with a torque screwdriver or torque wrench.
- If combining with a tool with a deep bit insertion depth, use the **SKABA** Adapter for Short Bit.
 - ➔ P.xxxx

* The hexalobular shape is prescribed by JIS B 1015:2008 (ISO 10664:2005) "Hexalobular internal driving feature for bolts and screws".



● Application

Installing and removing hexalobular socket head screws


Part Number	Hexalobular Socket No.	A	L	B	Mass (g)	Qty per Pack
SKXB-4	4	2.0	25	6.35	4.5	1
SKXB-5	5	3.0	25	6.35	4.6	1
SKXB-6	6	3.0	25	6.35	4.6	1
SKXB-8	8	3.0	25	6.35	4.7	1
SKXB-10	10	4.0	25	6.35	4.8	1
SKXB-15	15	4.0	25	6.35	4.9	1
SKXB-20	20	5.0	25	6.35	5.2	1
SKXB-25	25	5.0	25	6.35	5.2	1
SKXB-30	30	6.0	25	6.35	5.6	1

Unit : mm

● **SRD** Dedicated magnet screwdriver

Unit : mm

Part Number	L1	B1	Mass (g)	per Pack Qty
SRD-6.35	210	6.35	98	1



● Applicable Hexalobular Socket Head Screws

Part Number	Applicable Hexalobular Socket Head Screws									
	SSTS ➔P.xxxx	SET ➔P.xxxx	SETS	SLT ➔P.xxxx	SLTS	SLEC-A ➔P.xxxx	SLEC-B ➔P.xxxx	SNPXS ➔P.xxxx	SNFXS ➔P.xxxx	SET-TZB(INCH) ➔P.xxxx
SKXB-4			SETS-M2							
SKXB-5	SSTS-M2		SETS-M2.6							
SKXB-6	SSTS-M2.5	SET-M3	SETS-M3		SLTS-M2			SNPXS-M2	SNFXS-M2	SET-#6 - 32-TZB
SKXB-8	SSTS-M3	SET-M4	SETS-M4		SLTS-M2.5			SNPXS-M2.5	SNFXS-M2.5	SET-#8 - 32-TZB SET-#10 - 24-TZB SET-#10 - 32-TZB
SKXB-10	SSTS-M4	SET-M5	SETS-M5	SLT-M3-TZB	SLTS-M3	SLEC-M3-A	SLEC-M3-B	SNPXS-M3	SNFXS-M3	
SKXB-15	SSTS-M5					SLEC-M4-A	SLEC-M4-B			
SKXB-20	SSTS-M6		SETS-M6	SLT-M4-TZB	SLTS-M4	SLEC-M5-A	SLEC-M5-B	SNPXS-M4	SNFXS-M4	
SKXB-25	SSTS-M8			SLT-M5-TZB	SLTS-M5	SLEC-M6-A	SLEC-M6-B	SNPXS-M5	SNFXS-M5	
SKXB-30				SLT-M6-TZB	SLTS-M6	SLEC-M8-A	SLEC-M8-B	SNPXS-M6	SNFXS-M6	

● Part number specification

SKXB-4



1 Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
1 pc. in 1 bag	Not Available	Not Available	Not Available	Not Available