


# SPC-P Plastic Screw - Cross Recessed Pan Head Machine Screws - PC Additional Size



WEB Selection Tool    WEB CAD Download



● Material/Finish

RoHS2 Compliant

	<b>SPC-P</b>
Main body	PC (Polycarbonate) (Transparent)*1
Heat Resistance Temperature*2	115°C

- \*1: **SPC-M1.7-3-P** | **SPC-M1.7-4-P** are black.
- \*2: This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Max. Operating Temperature\*2 (min./max.): -40/115°C
- PC has low water absorbency and excellent weather resistance.
- The properties and precautions of plastic screws  
→ P.xxxx
- Application

Electrical and electronic equipment and automobiles

Unit : mm

Part Number	M	L														D1	L1	Tension*1 Rupture Load (N)	Torsional*1 Torque (N·m)	Mass (g)	
<b>SPC-M1.7-P</b>	M1.7	3	4														2.5	0.5	47	0.02	0.0066 - 0.0085
<b>SPC-M2-P</b>	M2	3	4	5	6	8	10	12									3.5	1.3	112	0.05	0.02 - 0.053
<b>SPC-M2.6-P</b>	M2.6	3	4	5	6	8	10	12	15								4.5	1.7	227	0.12	0.052 - 0.1
<b>SPC-M3-P</b>	M3		4	5	6	8	10	12	15	20	25	30					5.5	2	300	0.22	0.075 - 0.26
<b>SPC-M4-P</b>	M4			5	6	8	10	12	15	20	25	30		40			7	2.6	515	0.54	0.16 - 0.62
<b>SPC-M5-P</b>	M5				6	8	10	12	15	20	25	30	35				9	3.3	750	1.03	0.36 - 0.91
<b>SPC-M6-P</b>	M6						10	12	15	20	25	30	35	40			10.5	3.9	1080	1.37	0.6 - 1.6
<b>SPC-M8-P</b>	M8							12	15	20	25	30		40	14		5.2	1470	2.94	1.7 - 3.1	

- \*1: Values in chart are for reference only. They are not guaranteed values. The recommendation torque is 50% of the torsional torque.
- M1.7 is black.

Part Number	Qty per pack*1
<b>SPC-M1.7-P</b>	50
<b>SPC-M2-P</b>	50
<b>SPC-M2.6-P</b>	50
<b>SPC-M3-P</b>	50
<b>SPC-M4-P</b>	50
<b>SPC-M5-P</b>	50
<b>SPC-M6-P</b>	20
<b>SPC-M8-P</b>	20

\*1: Also sold separately from 1 piece up. → P.xxxx

● Part number specification

## SPC-M5-20-P



Order in number of packs.  
Also sold separately from 1 piece up. → P.xxxx

Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available	Not Available