

#### ● Application

Prevention of damage to screw heads and reliable tightening

#### ● Material/Finish

RoHS2 Compliant

	SNFXS
Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50




- Hexalobular socket shapes\*1 are designed to withstand high tightening torque compared to cross-recesses. → P.xxxx
- Screw heads are unlikely to be damaged due to tightening, allowing safe and secure tightening to be performed.
- Mounting/removing with regular tools such as hex keys and screwdrivers is not possible. Also usable for applications including prevention of disassembly, theft, or tampering for devices or facilities.\* 2
- Install and remove with **SKX** Dedicated Wrench or **SKXB** Dedicated Bit and **SRD** Dedicated Magnetic Screwdriver together.
- Use the **SKX-N** hexalobular wrench for extremely limited access spaces for mounting and removing in tight spaces.

\*1 : The hexalobular shape is prescribed by JIS B 1015: 2008(ISO 10664: 2005)"Hexalobular internal driving feature for bolts and screws".

\*2 : Tools for hexalobular sockets are commercially available. When tampering prevention is the main objective, consider tamper resistant screws. → P.xxxx

Unit : mm

Part Number	M	L 										D <sub>1</sub>	L <sub>1</sub>	Applicable wrench	Hexalobular Socket No.	t	Mass (g)
SNFXS-M2	M2	4	5	6	8	10	12					3.8	1.2	SKX-6	6	0.64	0.14 - 0.29
SNFXS-M2.5	M2.5	4	5	6	8	10	12	16				4.7	1.5	SKX-8	8	0.79	0.27 - 0.65
SNFXS-M3	M3		5	6	8	10	12	16	20			5.5	1.65	SKX-10	10	0.83	0.49 - 1.1
SNFXS-M4	M4			6	8	10	12	16	20	25		8.4	2.7	SKX-20	20	1.53	1 - 2.5
SNFXS-M5	M5				8	10	12	16	20	25	30	9.3	2.7	SKX-25	25	1.51	2.2 - 4.8
SNFXS-M6	M6					10	12	16	20	25	30	11.3	3.3	SKX-30	30	1.78	3.9 - 7.4

Part Number	Qty*1 per pack
<b>SNFXS-M2</b>	20
<b>SNFXS-M2.5</b>	20
<b>SNFXS-M3</b>	20
<b>SNFXS-M4</b>	20
<b>SNFXS-M5</b>	20
<b>SNFXS-M6</b>	20

\*1 : Also sold separately from 1 piece up. → P.xxxx

Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available

#### ● Related Products

**SKX** Hexalobular Wrench

→ P.xxxx



**SKX-N** Hexalobular Wrench for Extremely Limited Access Spaces

→ P.xxxx



**SKXB** Hexalobular Short Bit

→ P.xxxx



**SRD** Magnet Screwdriver

→ P.xxxx



#### ● Part number specification

**SNFXS-M5 - 20**

1 2

Order in number of packs.

Also sold separately from 1 piece up. → P.xxxx