


# SRWFS Triwing Flat Head Machine Screws **NEW**



WEB Selection Tool  
 WEB CAD Download  
 Tamper Resistance  
 SUS Stainless steel



● Material/Finish  RoHS2 Compliant

	<b>SRWFS</b>
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

● Part number specification

## SRWFS-M5 - 16



Order in number of packs.  
The minimum order is 1 piece. → P.xxxx

- This prevents mounting and removing with regular tools.
- Install and remove with **SRWB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.

● Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Part Number	M (Coarse)		L												D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)
	Nominal of Thread	Pitch	5	6	8	10	12	16	20	25	30	40	50						
<b>SRWFS-M2</b>	M2	0.4	5	6	8										3.8	1.2	SRWB-1	SRD-6.35	0.16 - 0.21
<b>SRWFS-M3</b>	M3	0.5		6	8	10	12	16	20	25					5.5	1.65	SRWB-2	SRD-6.35	0.53 - 1.4
<b>SRWFS-M4</b>	M4	0.7		6	8	10	12	16	20	25	30				8.4	2.7	SRWB-4	SRD-6.35	1.1 - 2.9
<b>SRWFS-M5</b>	M5	0.8				10	12	16	20	25	30	40	50		9.3	2.7	SRWB-5	SRD-6.35	2.5 - 7.4
<b>SRWFS-M6</b>	M6	1				10	12	16	20	25	30	40	50	11.3	3.3	SRWB-6	SRD-6.35	3.9 - 12	
<b>SRWFS-M8</b>	M8	1.25						16	20	25	30	40	50	15.8	4.65	SRWB-7	SRD-6.35	11 - 23	

Unit : mm

Part Number	L												Qty per Pack	
	5	6	8	10	12	16	20	25	30	40	50			
<b>SRWFS-M2</b>	●	●	●											10
<b>SRWFS-M3</b>		●	●	●	●	●	●	●	●					10
<b>SRWFS-M4</b>		●	●	●	●	●	●	●	●	●				10
<b>SRWFS-M5</b>				●	●	●	●	●	●	●	●			10
<b>SRWFS-M6</b>				●	●	●	●	●	●	●	●	●		10
<b>SRWFS-M8</b>						●	●	●	●	●	●	●	●	10

● The minimum order is 1 piece. → P.xxxx

● **SRWB** Dedicated bit

Unit : mm

Part Number	L	B	Mass (g)	Qty per Pack
<b>SRWB-1</b>	25.4	6.35	4.7	1
<b>SRWB-2</b>	25.4	6.35	4.8	1
<b>SRWB-4</b>	25.4	6.35	5.2	1
<b>SRWB-5</b>	25.4	6.35	5.6	1
<b>SRWB-6</b>	25.4	6.35	6.2	1
<b>SRWB-7</b>	25.4	6.35	6.6	1

**SRWB**




● **SRD** Dedicated magnet screwdriver

Unit : mm

Part Number	L	B	Mass (g)	Qty per Pack
<b>SRD-6.35</b>	210	6.35	98	1

**SRD**



Individual Sales → P.xxxx  
 Cleanroom Wash & Packaging → P.xxxx  
 Screw Length Adjustment → P.xxxx  
 Vibration Resistant → P.xxxx  
 Modification process for captive use → P.xxxx

Available / Add'l charge   Available / Add'l charge   Available / Add'l charge   Available / Add'l charge   Not Available