




# SLHS Socket Head Cap Screws with Low Profile - SUSXM7

Protrusion **SUS** Stainless steel



- Socket head cap screws have low head heights.
- Intended for reducing the size of devices and applications with limited overhead space.
- Also, **[SVLS]** Socket Head Cap Screws with Low Profile with Ventilation Hole is available.
- **[SLHS-UCL]** with cleanroom washing/cleanroom packing provided are available for some sizes.
- Conforms to DIN 7984.

## Application

Reducing the size of equipment and devices

## Material/Finish



	SLHS
Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50 or more

## SLHS SUSXM7

Unit : mm

Part Number 1	M (Coarse)		L 2													D1				L1	B*2	t	L2*1	Max. Torque (N•m)	Mass (g)		Qty per pack
	Nominal of Thread	Pitch																									
SLHS-M2	M2	0.4	5	6	8	10	12									3.8	1.3	1.3	0.7	Full Thread	0.18	0.13 -	0.29	50			
SLHS-M2.5	M2.5	0.45	5	6	8	10	12									4.5	1.6	1.5	1	Full Thread	0.36	0.26 -	0.47	50			
SLHS-M3	M3	0.5	5	6	8	10	12	16	20							5.5	2	2	1.5	12 (L=20)	0.6	0.5	-	1.2	50		
SLHS-M4	M4	0.7		6	8	10	12	16	20	25						7	2.8	2.5	2.3	Full Thread	1.5	1.1	-	2.8	50		
SLHS-M5	M5	0.8			8	10	12	16	20	25	30	35				8.5	3.5	3	2.7	16 (L≥30)	3.1	1.8	-	5.7	50		
SLHS-M6	M6	1			8	10	12	16	20	25	30	35	40	45		10	4	4	3	18 (L≥30)	5.3	3.1	-	11	20		
SLHS-M8	M8	1.25				10	12	16	20	25	30	35	40	45	50	13	5	5	3.8	22 (L≥35)	12	7.2	-	22	20		
SLHS-M10	M10	1.5						16	20	25	30	35	40	45	50	16	6	6	4.5	32 (L≥45)	25	15	-	33	10		

\*1: If the "L" value is other than the value in parentheses, the screw is full thread.

\*2: The hexagonal width across flat of **[SLHS-M10]** has been changed from 7 mm to 6 mm.

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

## Part number specification

**SLHS-M5-20**

1

2

1 Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge