





SSC-SNHS Hexagon Head Captive Screws

WEB Selection Tool WEB CAD Download SUS Stainless steel



- Installation example
Machine a screw hole on the cover and let through the threaded part of **SSC-SNHS**. Threaded part of **SSC-SNHS** is still engaged with the screw hole on the cover even after the screw is removed from the frame, so **SSC-SNHS** never fall out of the cover.



SSC-SNHS Hex Head Captive Screws

⚠ Precautions for Use

- Screw hole inner diameter on the cover side shall be at least the dc dimension.
- The cover thickness should be 0.8 mm or above.
- Part number specification

SSC-SNHS-M6-12



- It prevents fall-off and loss of the screw. For fixing of protection cover and cover for inspection that are frequently mounted and removed.
- Hex head bolt type.
- For CE marking. → P.xxxx
- We also produce captive screws of special specifications, e.g. dimensions, shapes, materials and surface treatment. Please feel free to contact our customer service.



● Application

Fixing of protection cover and cover for inspection / CE marking
Machine tool / Food machinery / and Electronic device

● Material/Finish

RoHS2 Compliant

	SSC-SNHS
Main body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50

Unit : mm

Part Number 1	M (Coarse)		L 2	Lm	B	L1	dc	Mass (g)
	Nominal of Thread	Pitch						
SSC-SNHS-M3	M3	0.5	8 10 12 16	4	5.5	2	2.2	0.8 - 1.1
SSC-SNHS-M4	M4	0.7	10 12 16 20	5	7	2.8	3	1.7 - 2.5
SSC-SNHS-M5	M5	0.8	12 16 20 25	6	8	3.5	3.9	3 - 4.7
SSC-SNHS-M6	M6	1	12 16 20 25 30	8	10	4	4.5	4.9 - 8.1
SSC-SNHS-M8	M8	1.25	16 20 25 30 35 40	10	13	5.5	6.3	11 - 20

Part Number	Qty per pack
SSC-SNHS-M3	1
SSC-SNHS-M4	1
SSC-SNHS-M5	1
SSC-SNHS-M6	1
SSC-SNHS-M8	1

1 Individual Sales → P.xxxx	1 Cleanroom Wash & Packaging → P.xxxx	1 Screw Length Adjustment → P.xxxx	1 Vibration Resistant → P.xxxx	1 Modification process for captive use → P.xxxx
1 unit in 1 bag	Available / Add'l charge	Not Available	Not Available	with Captive Processing