


- Male screw knobs can be created through combination with commercial hex socket bolts. Screw length is freely selectable depending on the hex socket bolt used.

- Use hex socket bolts with head dimensions as indicated below.

M	s1	K
M6	10	4
M8	13	5.5

Unit : mm



- Knob bodies and hubs are metal. Suitable for applications in equipment and devices using metal detectors as foreign matter entry countermeasures. \*1

\*1: Confirm that the metal detector reacts to aluminum alloys and stainless steel.

- Use the dedicated jig **KSKA-W** for assembly. The jig is made of resin and will not damage the knob body.

- We also manufacture male screw knob products assembled with hex socket bolts. Please contact our customer service.

- Material/Finish RoHS2 Compliant

	KSKA
Knob Main Body	Aluminum Alloy Anodized
Hub	SUS304

**⚠ Precautions for Use**


- Do not use the knob as a way to pick up workpieces. The knob and hub may come apart.
- After use, carefully wipe away any moisture or dirt. If moisture or dirt containing sodium remains on the knob, it may cause corrosion.

Unit : mm

Part Number	D	M	H	A	s	d	d1	B	Lh	Mass (g)
<b>KSKA-32-M6</b>	32	M6	22	11	11	14	6.7	10	15	29
<b>KSKA-40-M8</b>	40	M8	24	14	10	18	8.7	13	15	54




• **Assembling method**



• **KSKA-W** dedicated jig

Part Number	L	Applicable Screw Length max.	Mass (g)
<b>KSKA-3240W-S</b>	32	45	200
<b>KSKA-3240W-L</b>	52	65	300

Unit : mm



• **Material/Finish**

	KSKA-W
Knob Side	Polyacetal (White)
Hub Side	SUS304
Magnet	Neodymium



• **Part number specification**

**KSKA-32-M6**



Cleanroom Wash & Packaging → P.0000	Screw Combination → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Laser Marking → P.0000
Not Available	Not Available	Not Available	Not Available	Available / Add'l charge