






SNZ-TBZ-ALK



SNZS-ALK M1 - M1.7



SNZS-ALK M2 - M2.6



*1: For **SNZS-ALK** with dimension L of under 4 mm, nylon patch is on one side.



- M1-M2.6. Miniature screw with nylon patch for precision instruments.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- Pan head machine screw type with low head height. For applications with limited overhead space.

Application

Reducing the size of equipment and devices / Compact precision instruments / Return and fall prevention of screws

Material/Finish



	SNZ-TBZ-ALK	SNZS-ALK
Main Body	SWCH16A Black Trivalent Chromate Treatment	SUSXM7 (Equivalent to SUS304)
Nylon Patch	Nylon 11	Nylon 11

SNZ-TBZ-ALK Made of Steel

Unit : mm

Part Number 1	M (Coarse)		L 2								D1	L1	s*1	L2	Max. Tightening Torque (N·m)	Mass (g)
	Nominal of Thread	Pitch														
SNZ-M1.4-TBZ-ALK	M1.4	0.3	2		3		4	5	6	8	2	0.5	0.6	1.1	0.05	0.023 - 0.074
SNZ-M1.7-TBZ-ALK	M1.7	0.35	2		3		4	5	6	8	2.5	0.5	0.7	1.3	0.09	0.037 - 0.11
SNZ-M2-TBZ-ALK	M2	0.4	2	2.5	3	3.5	4	5	6	8	3	0.6	0.8	1.6	0.18	0.055 - 0.16
SNZ-M2.6-TBZ-ALK	M2.6	0.45			3		4	5	6	8	4	0.8	0.9	2.1	0.39	0.14 - 0.3

*1: If L < 4, dimension s is 0.

Part Number	Qty*1 per Pack
SNZ-M1.4-TBZ-ALK	50
SNZ-M1.7-TBZ-ALK	50
SNZ-M2-TBZ-ALK	50
SNZ-M2.6-TBZ-ALK	50

*1: Also sold separately from 1 piece up. ➔ P.xxxx

SNZS-ALK Made of Stainless Steel

Unit : mm

Part Number 1	M (Coarse)		L 2								D1	L1	s*1	L2*2	Max. Tightening Torque (N·m)	Mass (g)
	Nominal of Thread	Pitch														
SNZS-M1-ALK	M1	0.25	2		3		4	5			1.8	0.45	0.5	0.7	0.01	0.014 - 0.026
SNZS-M1.4-ALK	M1.4	0.3	2		3		4	5	6	8	2	0.5	0.6	1.1	0.03	0.025 - 0.091
SNZS-M1.6-ALK	M1.6	0.35	2		3		4	5	6	8	2.3	0.5	0.7	1.2	0.05	0.036 - 0.15
SNZS-M1.7-ALK	M1.7	0.35	2		3		4	5	6	8	2.5	0.5	0.7	1.3	0.07	0.06 - 0.2
SNZS-M2-ALK	M2	0.4	2	2.5	3	3.5	4	5	6	8	3	0.6	0.8	1.6	0.12	0.08 - 0.28
SNZS-M2.5-ALK	M2.5	0.45			3		4	5	6	8	3.8	0.8	0.9	2	0.24	0.15 - 0.3
SNZS-M2.6-ALK	M2.6	0.45		2.5	3		4	5	6	8	4	0.8	0.9	2.1	0.28	0.16 - 0.33

*1: If L < 4, dimension s is 0.

Part Number	Qty*1 per Pack
SNZS-M1-ALK	50
SNZS-M1.4-ALK	50
SNZS-M1.6-ALK	50
SNZS-M1.7-ALK	50
SNZS-M2-ALK	50
SNZS-M2.5-ALK	50
SNZS-M2.6-ALK	50

*1: Also sold separately from 1 piece up. ➔ P.xxxx

Part number specification

SNZ-M2-3-TBZ-ALK

1 2 1

Order in number of packs.

Also sold separately from 1 piece up. ➔ P.xxxx

Individual Sales ➔ P.xxxx	Cleanroom Wash & Packaging ➔ P.xxxx	Screw Length Adjustment ➔ P.xxxx	Vibration Resistant ➔ P.xxxx	Modification process for captive use ➔ P.xxxx
Available / Add'l charge	S.S. only/ Add'l charge	Not Available	Not Available	Not Available