



SRTS Two Hole Pan Head Machine Screws

WEB Selection Tool


WEB CAD Download



Tamper Resistance

SUS

Stainless steel



- Part number specification

SRTS-M5-16



Order in number of packs.

The minimum order is 1 piece. → P.xxxx

- This prevents mounting and removing with regular tools.
- Install and remove with **[SRTB]** Dedicated Bits and **[SRD]** Dedicated Magnetic Screwdriver together.
- The simple head design is suitable for decoration.

Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

Material/Finish



	SRTS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

Part Number	M	L	D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)
SRTS-M3	M3	6 8 10	6	1.8	SRTB-4	SRD-6.35	0.66 - 0.82
SRTS-M4	M4	10 12 16	8	2.4	SRTB-8	SRD-6.35	1.7 - 2.2
SRTS-M5	M5	12 16 20	10	3	SRTB-10	SRD-6.35	3.4 - 4.3

Unit : mm


Part Number	L	Qty per Pack
SRTS-M3	6 8 10 12 16 20	20
SRTS-M4	10 12 16 20	20
SRTS-M5	12 16 20	20

- The minimum order is 1 piece. → P.xxxx

[SRTB] Dedicated Bit

Unit : mm


Part Number	L	B	Mass (g)	Qty per Pack
SRTB-4	25.4	6.35	5	1
SRTB-8	25.4	6.35	5	1
SRTB-10	25.4	6.35	5.2	1



[SRD] Dedicated Magnet Screwdriver

Unit : mm

Part Number	L	B	Mass (g)	Qty per Pack
SRD-6.35	210	6.35	98	1



1 Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge