




SPVC-N



SPVC-W



- These products have excellent chemical resistance against strong acids and organic solvents as well as halogen compounds such as hydrogen sulfide and bromine.
- They can be used in atmospheres in which metal and PVC (polyvinyl chloride) cannot be used.
- Max. Operating Temperature\*2 (min./max.):  
-10/35 deg C
- Two colors, ivory and gray, are available. 

**IV** ————— Ivory

**GR** ————— Gray

- The properties and precautions of plastic screws  
→ P.xxxx
- Application

FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, and chemical plants

- Material/Finish 


SPVC-N / SPVC-W	
Main body	H-PVC (Hard Polyvinyl Chloride) *1
Heat Resistance Temperature*2	35°C

\*1: Does not comply with the RoHS Directive. These products contain lead.

\*2: This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

SPVC-N Hex Nuts

Unit : mm

Part Number	M (Coarse)		B	T	Mass (g)	Qty per pack
	Nominal of Thread	Pitch				
 <b>SPVC-M4-N</b>	M4	0.7	7	3.2	0.14	1
<b>SPVC-M5-N</b>	M5	0.8	8	4.7	0.24	1
<b>SPVC-M6-N</b>	M6	1	10	5.2	0.44	1

SPVC-W Washers

Unit : mm






Part Number	d	D	t	Nominal	Mass (g)	Qty per pack
<b>SPVC-4-W</b>	4.3	9	0.8	4	0.053	1
<b>SPVC-5-W</b>	5.3	10	1	5	0.077	1
<b>SPVC-6-W</b>	6.4	12.5	1.6	6	0.2	1

- Part number specification

**SPVC-M5-N-IV**





 Individual Sales → P.xxxx	 Cleanroom Wash & Packaging → P.xxxx	 Screw Length Adjustment → P.xxxx	 Vibration Resistant → P.xxxx	 Modification process for captive use → P.xxxx
1 pc. in 1 bag	Available / Add'l charge	Not Available	Not Available	Not Available