




SPA-Z Plastic Threaded Rod - RENY

High strength High Specific Strength



- RENY™ is a thermoplastic engineering plastic with excellent tensile and bending strength.
- It is highly fatigue-resistant and has excellent creep and heat insulation properties.
- While it is nearly as strong as metal, its weight is approximately 1/5 of iron.
- The properties and precautions of plastic screws

Application

Heat insulation and dew condensation prevention of electric and electronic devices and refrigerating and freezing facilities / Weight saving of offshore instruments, plating facilities, automobiles, airplanes, aerospace devices, etc.

Material/Finish



	SPA-Z
Main Body	RENY™*1 (50% Glass Fiber Reinforced Polyamide MXD6) (Ivory)
Heat Resistance Temperature*2	105°C

*1 : RENY™ is a trademark or registered trademark of Mitsubishi Gas Chemical Company, Inc.

*2 : This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.

Unit : mm

Part Number ◀1	M (Coarse)		L	Tension Rupture Load*1 (N)	Mass (g)
	Nominal of Thread	Pitch			
SPA-M6-Z	M6	1	300	3106	11
SPA-M8-Z	M8	1.25	300	5335	20
SPA-M10-Z	M10	1.5	300	7646	31
SPA-M12-Z	M12	1.75	300	7511	45
SPA-M16-Z	M16	2	300	19987	81

*1 : Values in chart are for reference only. They are not guaranteed values.

Part number specification

SPA-M6-Z

◀1

1 Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
1 piece in 1 pack	Available / Add'l charge	Not Available	Not Available	Not Available