




# SSCPS Cross Recessed Pan Head Captive Machine Screws

WEB Selection Tool


WEB CAD Download

SUS Stainless steel



## ● Installation example

Make a screw hole in the cover, then pass **SSCPS** thread through it. Even when the screw is removed from the frame, **SSCPS** does not fall out from the cover because **SSCPS** thread catches on the screw hole of the cover.



**SSCPS** Cross Recessed Pan Head Captive Machine Screw



- The shape of the screws prevent them from falling out and loss. They are intended to fix protective and inspection covers that are frequently installed and removed.
- Cross Recessed pan head machine screws.
- These items comply with CE marking requirements.  
→ P.xxxx
- Application

Securement of protective and inspection covers and compliance with CE marked products.

Machine tools, food industry machines, and electrical and electronic equipment

## ● Material/Finish

RoHS2 Compliant

	<b>SSCPS</b>
Main Body	SUSXM7 (Equivalent to SUS304)
Strength Class	A2-50

## ⚠ Precautions for Use

- The inner diameter of the screw hole of the cover must be equal or larger than dimension dc.
- The thickness of the cover must be 0.8 mm or more.

Unit : mm

Part Number	1	M	L	2							Lm	D1	L1	dc	Mass (g)
<b>SSCPS-M3</b>		M3	8	10	12	16					4	5.5	2	2.2	0.61 - 0.94
<b>SSCPS-M4</b>		M4		10	12	16	20				5	7	2.6	3	1.3 - 2.1
<b>SSCPS-M5</b>		M5			12	16	20	25			6	9	3.3	3.9	2.7 - 4.2
<b>SSCPS-M6</b>		M6			12	16	20	25	30		8	10.5	3.9	4.6	4.3 - 7.4
<b>SSCPS-M8</b>		M8				16	20	25	30	35	40	10	14	5.2	10 - 18

Part Number	Qty per pack
<b>SSCPS-M3</b>	1
<b>SSCPS-M4</b>	1
<b>SSCPS-M5</b>	1
<b>SSCPS-M6</b>	1
<b>SSCPS-M8</b>	1

## ● Part number specification

**SSCPS-M6-12**

1 2

1 Individual Sales → P.xxxxx	Cleanroom Wash & Packaging → P.xxxxx	Screw Length Adjustment → P.xxxxx	Vibration Resistant → P.xxxxx	Modification process for captive use → P.xxxxx
1 unit in 1 bag	Available / Add'l charge	Not Available	Not Available	with Captive Processing