


SADS-SD Screw Adaptor - Thread Size Conversion Type



WEB Selection Tool

WEB CAD Download

SUS Stainless steel



● Material/Finish

RoHS2 Compliant

	SADS-SD
Thread Part	SUS303
Stopper Ring	Equivalent to SUS304

- By combining with female screw products such as a lever and knob, this may be used as a lever or knob of any non-standard screw diameter.
- For screw fixing, use a pin stopper or anaerobic adhesive agent.
- If it is repeatedly tightened in combination with a lever or knob, a pin stopper is recommended.
- Use a stopper ring to accurately determine the threaded length.

Dimensions

Unit : mm

Part Number	M (coarse) ◀1	M1 (coarse) ◀2	Lm	s	t	D	Mass (g)
SADS-M4-M5-SD	M4	M5	4.5	1.4	0.6	7	1.9 - 6.7
SADS-M5-M4-SD	M5	M4	4.5	1.6	0.6	7	1.5 - 3.1
SADS-M5-M6-SD	M5	M6	4.5	1.6	0.6	9	2.7 - 12
SADS-M6-M5-SD	M6	M5	5.5	1.6	0.6	9	2.5 - 7.3
SADS-M6-M8-SD	M6	M8	5.5	2	0.6	9	4.9 - 27
SADS-M8-M6-SD	M8	M6	6.5	2	0.6	9	4.3 - 13
SADS-M8-M10-SD	M8	M10	6.5	2.5	0.8	12	10 - 43
SADS-M10-M8-SD	M10	M8	8.5	2.5	0.8	12	8.2 - 30
SADS-M10-M12-SD	M10	M12	8.5	3	0.8	16	16 - 64

SADS-SD Made of Stainless Steel

Part Number	L (mm) ◀3									
	12	16	20	25	32	40	50	63	80	
SADS-M4-M5-SD	●	●	●	●	●	●	●			
SADS-M5-M4-SD	●	●	●	●	●					
SADS-M5-M6-SD	●	●	●	●	●	●	●			
SADS-M6-M5-SD	●	●	●	●	●	●	●			
SADS-M6-M8-SD	●	●	●	●	●	●	●	●	●	
SADS-M8-M6-SD	●	●	●	●	●	●	●	●		
SADS-M8-M10-SD		●	●	●	●	●	●	●	●	
SADS-M10-M8-SD	●	●	●	●	●	●	●	●	●	
SADS-M10-M12-SD		●	●	●	●	●	●	●	●	

● Part number specification

SADS-M10-M12-80-SD

Product Code ◀1 ◀2 ◀3 Thread Size Conversion Type

Cleanroom Wash & Packaging → P.xxxx
Available / Add'l charge

Screw Combination → P.xxxx
Available / Add'l charge

Screw Length Adjustment → P.xxxx
Available / Add'l charge

Vibration Resistant → P.xxxx
Available / Add'l charge