


# SNZF-TZB-ALK

Cross Recessed Micro Flat Head Machine Screws with Nylon Patch - Type 0 - 1



Vibration resistant treatment Miniature Size



● Material/Finish



SNZF-TZB-ALK	
Main Body	Steel Trivalent Chromate Treatment
Nylon Patch	Nylon 11

- Miniature screws with nylon patch for precision instruments (Type 0 - 1).
- M1.4 - M2.6.
- Head is more compact than standard flat head machine screws.
- The friction of the nylon adhered to the thread suppresses the return rotation of the thread.
- Even if the tightening force is lost, the return rotation is suppressed, preventing the screws from falling off.
- The heat resistant temperature of the nylon patch is 120°C.

● Application

For making devices and equipment more compact  
Screw return and fallout prevented  
Compact precision equipment

Unit : mm


Part Number	M (Coarse)		L								D1	L1	Cross-recessed Socket No.	Max. Tightening Torque (N·m)*1	Mass (g)	Qty per Pack
	Nominal of Thread	Pitch	2.5	3	3.5	4	5	6	8	10						
<b>SNZF-M1.4-TZB-ALK</b>	M1.4	0.3	2.5	3	3.5	4	5	6	8	10	2.0	0.45	0	0.05	0.02 - 0.08	50
<b>SNZF-M1.6-TZB-ALK</b>	M1.6	0.35	2.5	3	3.5	4	5	6	8		2.4	0.5	0	0.07	0.03 - 0.09	50
<b>SNZF-M1.7-TZB-ALK</b>	M1.7	0.35	2.5	3	3.5	4	5	6	8	10	2.5	0.5	0	0.09	0.04 - 0.13	50
<b>SNZF-M2-TZB-ALK</b>	M2	0.4		3	3.5	4	5	6	8	10	3.0	0.6	0	0.18	0.06 - 0.18	50
<b>SNZF-M2.5-TZB-ALK</b>	M2.5	0.45		3		4	5	6			3.8	0.8	0	0.32	0.1 - 0.19	50
<b>SNZF-M2.6-TZB-ALK</b>	M2.6	0.45		3		4	5	6	8	10	4.0	0.8	0	0.39	0.12 - 0.33	50

\*1 : Values in chart are for reference only. They are not guaranteed values.

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

**SNZF-M2-3-TZB-ALK**



Individual Sales Available / Add'l charge	Cleanroom Wash & Packaging Available / Add'l charge	Screw Length Adjustment Not Available	Vibration Resistant Not Available	Modification process for captive use Not Available
--	--	--	--------------------------------------	---