

• M1 - M2.5.

Miniature screws for precision instruments.

• Application

Reducing the size of equipment and devices
Compact precision instruments


• Material/Finish



	SNS	SNSS
Main Body	SCM435 Ferrosoferric Oxide Coating (Black)	SUSXM7 (Equivalent to SUS304)

• Usage example

For fixing miniature linear guideway rails and tables.



Unit : mm

SNS Steel - Ferrosoferric Oxide Coating		SNSS Stainless steel		Common dimensions										Qty per Pack		
Part Number	Max. Torque (N·m)	Part Number	Max. Torque (N·m)	M (Coarse)		L				D ₁	L ₁	B	Mass (g)			
				Nominal of Thread	Pitch											
		SNSS-M1	0.02	M1	0.25	2	3	4	5		2	1	0.9	0.025 - 0.039	10	
		SNSS-M1.4	0.07	M1.4	0.3	2	3	4	5		2.6	1.4	1.3	0.062 - 0.085	10	
SNS-M1.6	0.25	SNSS-M1.6	0.1	M1.6	0.35		3	4	5	6	3	1.6	1.5	0.09 - 0.12	10	
SNS-M2	0.53	SNSS-M2	0.22	M2	0.4		3	4	5	6	3.8	2	1.5	0.16 - 0.22	10	
SNS-M2.5	1.12	SNSS-M2.5	0.46	M2.5	0.45			4	5	6	8	4.5	2.5	2	0.35 - 0.47	10

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• Part number specification

SNSS-M2 - 3



Individual Sales → P. xxxxx	Cleanroom Wash & Packaging → P. xxxxx	Screw Length Adjustment → P. xxxxx	Vibration Resistant → P. xxxxx	Modification process for captive use → P. xxxxx
Available / Add'l charge	S.S. only/ Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available