

*: Check the A dimension based on the distance from the mounting surface to the top surface of the table and select accordingly.

Material/Finish



	NLSCNS
Main Body	SUS304
Hex Socket Head Cap Screw	SUSXM7


- Stoppers for linear guides with threaded holes (fine) machined.
- In combination with fine screw thread stopper bolts*1, fine adjustment of the screw-in depth is easy.
- Made of stainless steel. Suitable for environments where corrosion resistance is required.
- Supported rail sizes are 15 mm/20 mm/25 mm/30 mm/35 mm.
- Hex socket head cap screws for mounting are provided with all products.

*1: Stopper bolts are not provided. The customer is asked to prepare them.

Application

Table position adjustment
Table retention and fall prevention
Stoppers for emergencies

Usage Example



- Use the lock nut on the opposite side of the side that receives the force.



Unit : mm

Part Number	W	H	A	B	J	P	T	M (Fine)	Nominal of Thread	Pitch	D	Hex Socket Head Cap Screw	Mass (g)
NLSCNS-01	50	30	23.5	12	18	35	12	M6		0.75	5.5	M5×16	84.1
NLSCNS-02	50	38	31.5	12	18	35	12	M6		0.75	5.5	M5×16	97.5
NLSCNS-03	50	43	35.5	12	18	35	12	M6		0.75	5.5	M5×16	106.5
NLSCNS-04	50	35	27.5	12	20	35	12	M8		1.0	5.5	M5×16	94.6
NLSCNS-05	50	43	35.5	12	20	35	12	M8		1.0	5.5	M5×16	109.4
NLSCNS-06	50	45	37.5	12	20	35	12	M8		1.0	5.5	M5×16	113.3
NLSCNS-07	50	40	32.5	16	20	35	16	M8		1.0	6.6	M6×20	152.6
NLSCNS-08	50	48	40.5	16	20	35	16	M8		1.0	6.6	M6×20	172.5
NLSCNS-09	50	51	43.5	16	20	35	16	M8		1.0	6.6	M6×20	180.5
NLSCNS-10	65	57	49.5	16	24	45	16	M8		1.0	9	M8×20	244.2
NLSCNS-11	65	63	55.5	16	24	45	16	M8		1.0	9	M8×20	261.9

Related Products

Stopper bolts **NSBFH** are available.

Rounded head type stopper bolts **NSBRH** are available.

Stopper bolts with urethane pad **NSBUH** are available.



Part Number Specification

NLSCNS-03



Cleanroom Wash & Packaging	Screw Combination	Screw Length Adjustment	Vibration Resistant	Laser Marking
Please feel free to contact us	Not Available	Not Available	Not Available	Available / Add'l charge