




SRTS Two Hole Pan Head Machine Screws

Tamper Resistance **SUS** Stainless steel



- This prevents mounting and removing with regular tools.
- Install and remove with **SRTB** Dedicated Bits and **SRD** Dedicated Magnetic Screwdriver together.
- The simple head design is suitable for decoration.

• Application

Machinery / Tools / Equipment / Devices disassembly prevention / Tampering prevention / Theft prevention for outdoor facilities / Security measures / Safety measures

• Material/Finish



	SRTS
Main Body	Equivalent to SUS304
Strength Class	Equivalent to A2-50

Unit : mm

Part Number 1	M (Coarse)		L 2						D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)	Qty per Pack	
	Nominal of Thread	Pitch	6	8	10	12	16	20							
SRTS-M3	M3	0.5							6	1.8	SRTB-4	SRD-6.35	0.66 - 0.82	20	
SRTS-M4	M4	0.7				10	12	16		8	2.4	SRTB-8	SRD-6.35	1.7 - 2.2	20
SRTS-M5	M5	0.8					12	16	20	10	3	SRTB-10	SRD-6.35	3.4 - 4.3	20

• When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

• **SRTB** Dedicated bit

Unit : mm

Part Number	L	B	Mass (g)
SRTB-4	25.4	6.35	5
SRTB-8	25.4	6.35	5
SRTB-10	25.4	6.35	5.2

SRTB




• **SRD** Dedicated magnet screwdriver

Unit : mm

Part Number	L	B	Mass (g)
SRD-6.35	210	6.35	98

SRD



• Part number specification

SRTS-M5-16



Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge