




# SNSL Hex Socket Head Cap Screws - SUS316L



## ● Material/Finish

	<b>SNSL</b>
Main Body	SUS316L
Strength Class	A4-70

- These screws have corrosion resistibility against chemical products and seawater environments that matches or exceeds SUS304.
- Nonmagnetic.
- SUS316L is a stainless steel made by adding Mo to SUS304, so it has high pitting corrosion and oxidation resistance. Due to its reduced carbon, it also has high intergranular corrosion resistibility.
- High strength even under high temperatures because of basic components include Mo.

## ● Application

FPD production equipment, semiconductor devices, aquatic applications, and general industrial machines

Unit : mm


Part Number 1	M (Coarse)		L 2										D1	L1	B	Mass (g)
	Nominal of Thread	Pitch	5	6	8	10	12	16	20	25	30	35				
<b>SNSL-M3</b>	M3	0.5	5	6	8	10	12	16					5.5	3	2.5	0.67 - 1.2
<b>SNSL-M4</b>	M4	0.7	5	6	8	10	12	16	20	25			7	4	3	1.4 - 3.2
<b>SNSL-M5</b>	M5	0.8		6	8	10	12	16	20	25			8.5	5	4	2.2 - 4.8
<b>SNSL-M6</b>	M6	1			8	10	12	16	20	25	30		10	6	5	4.3 - 8.3
<b>SNSL-M8</b>	M8	1.25					12	16	20	25	30	35	13	8	6	11 - 19

Part Number	Qty*1 per pack
<b>SNSL-M3</b>	5
<b>SNSL-M4</b>	5
<b>SNSL-M5</b>	5
<b>SNSL-M6</b>	5
<b>SNSL-M8</b>	5

\*1 : Also sold separately from 1 piece up. → P.xxxx

## ● Part number specification

### SNSL-M5-16



Order in number of packs.

Also sold separately from 1 piece up. → P.xxxx

Individual Sales → P.xxxx	Cleanroom Wash & Packaging → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Modification process for captive use → P.xxxx
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge