



- A flat-shaped tension lever. For applications with narrow top or bottom space.
- Since the rotating radius is large, a large clamping force can be achieved by small force.
- The phase angle of the lever in regards to the screw can be freely adjusted.

• Material/Finish

RoHS2 Compliant

	LFF
Lever Part	S45C Ferrosferric Oxide Film (Black)
Thread Part	S45C Ferrosferric Oxide Film (Black)
Grip	Phenol Resin (Black)

Unit : mm

Part Number	M (Coarse)	Lf	R	H	H'	h	s	A	B	D	d	Number of Teeth	Max. load*1 (N)	Max. clamping*1 force (kN)	Mass (g)
LFF-8	M8	18	100	12	16	19	2	10	25	33	13	22	120	10	160
LFF-10	M10	21	130	13.5	17.5	22	2	12	30	41	19	26	180	16	300
LFF-12	M12	21	130	13.5	17.5	22	2	12	30	41	19	26	300	23	300
LFF-16	M16	27	150	17	22	28	2	14	35	45	23	36	660	43	450

*1 : About the definition of max. load / max. clamping force → P.xxxx

• Related Products

Male screw type flat tension lever **LFM** is available.
→ P.xxxx



• Part number specification

LFF-16



Cleanroom Wash & Packaging → P.xxxx	Screw Combination → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Not Available	Not Available	Not Available	Not Available	Available / Add'l charge