



- Three types: Male Screw **KRM** **KRMS** / Female Screw **KRF** **KRFS** / Reamer Bore **KRR**.
- The reamer hole **KRR** hub has a guide hole for the fixing pin.
- A rich variety of thread sizes from M4 to M10 are available.
- Types and thread part materials can be selected by a product code.

Product Code	Type	Thread Part Material
<b>KRM</b>	Male Screw	Made of Steel
<b>KRMS</b>	Male Screw	Made of Stainless Steel
<b>KRF</b>	Female Screw	Made of Steel
<b>KRFS</b>	Female Screw	Made of Stainless Steel
<b>KRR</b>	Reamer Bore	Made of Steel

**KRM** **KRMS** Male Screw

Unit : mm

Part Number Made of Steel	Part Number Made of Stainless Steel	D	M (Coarse)		Lm	H	s	d	Mass (g)
			Nominal of Thread	Pitch					
<b>KRM-25-M4-6</b>		25	M4	0.7	6	19	8	13	6
<b>KRM-25-M4-10</b>		25	M4	0.7	10	19	8	13	7
<b>KRM-25-M4-16</b>		25	M4	0.7	16	19	8	13	7
<b>KRM-32-M5-10</b>	<b>KRMS-32-M5-10</b>	32	M5	0.8	10	22	10	15	11
<b>KRM-32-M5-16</b>	<b>KRMS-32-M5-16</b>	32	M5	0.8	16	22	10	15	12
<b>KRM-32-M5-20</b>	<b>KRMS-32-M5-20</b>	32	M5	0.8	20	22	10	15	12
<b>KRM-32-M6-10</b>		32	M6	1	10	22	10	15	12
<b>KRM-32-M6-20</b>		32	M6	1	20	22	10	15	14
<b>KRM-32-M6-40</b>		32	M6	1	40	22	10	15	19
<b>KRM-40-M6-10</b>	<b>KRMS-40-M6-10</b>	40	M6	1	10	25	11	17	16
<b>KRM-40-M6-16</b>	<b>KRMS-40-M6-16</b>	40	M6	1	16	25	11	17	18
<b>KRM-40-M6-20</b>	<b>KRMS-40-M6-20</b>	40	M6	1	20	25	11	17	18
<b>KRM-40-M6-25</b>	<b>KRMS-40-M6-25</b>	40	M6	1	25	25	11	17	19
<b>KRM-40-M8-16</b>		40	M8	1.25	16	25	11	17	23
<b>KRM-40-M8-20</b>		40	M8	1.25	20	25	11	17	25
<b>KRM-50-M8-16</b>	<b>KRMS-50-M8-16</b>	50	M8	1.25	16	30	13.5	20	29
<b>KRM-50-M8-20</b>	<b>KRMS-50-M8-20</b>	50	M8	1.25	20	30	13.5	20	31
<b>KRM-50-M8-25</b>	<b>KRMS-50-M8-25</b>	50	M8	1.25	25	30	13.5	20	33
<b>KRM-50-M8-30</b>	<b>KRMS-50-M8-30</b>	50	M8	1.25	30	30	13.5	20	35
<b>KRM-50-M8-50</b>		50	M8	1.25	50	30	13.5	20	43
<b>KRM-50-M10-20</b>		50	M10	1.5	20	30	13.5	20	40
<b>KRM-50-M10-30</b>		50	M10	1.5	30	30	13.5	20	46
<b>KRM-63-M10-20</b>		63	M10	1.5	20	35	15	23	55
<b>KRM-63-M10-30</b>	<b>KRMS-63-M10-30</b>	63	M10	1.5	30	35	15	23	61
<b>KRM-63-M10-50</b>	<b>KRMS-63-M10-50</b>	63	M10	1.5	50	35	15	23	73

• Material/Finish

RoHS2 Compliant

	<b>KRM</b>	<b>KRMS</b>	<b>KRF</b>	<b>KRFS</b>	<b>KRR</b>
Knob	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)
Thread Part	SWCH10R Trivalent Chromate Treatment	SUSXM7	Steel Trivalent Chromate Treatment	SUS303	
Hub					Steel Ferrosferric Oxide Film (Black)

**KRF** **KRFS** Female Screw

Unit : mm

Part Number Made of Steel	Part Number Made of Stainless Steel	D	M (Coarse)		Lf	H	s	d	Mass (g)
			Nominal of Thread	Pitch					
<b>KRF-25-M4</b>		25	M4	0.7	8	19	8	13	13
<b>KRF-32-M5</b>	<b>KRFS-32-M5</b>	32	M5	0.8	10	22	10	15	15
<b>KRF-32-M6</b>		32	M6	1	10	22	10	15	15
<b>KRF-40-M6</b>	<b>KRFS-40-M6</b>	40	M6	1	14	25	11	17	17
<b>KRF-40-M8</b>		40	M8	1.25	14	25	11	17	15
<b>KRF-50-M8</b>	<b>KRFS-50-M8</b>	50	M8	1.25	18	30	13.5	20	27
<b>KRF-50-M10</b>		50	M10	1.5	19	30	13.5	20	24
<b>KRF-63-M10</b>	<b>KRFS-63-M10</b>	63	M10	1.5	20	35	15	23	55

**KRR** Reamer Bore

Unit : mm

Part Number Made of Steel	D	C	Lc	H	C1	d2	d	f	h	s	Mass (g)
<b>KRR-40-R8</b>	40	8	15	25	2.8	19	14	7	9	11	27
<b>KRR-50-R10</b>	50	10	19	32	2.8	22	17	8	13	15.5	47
<b>KRR-63-R12</b>	63	12	23	40	3.8	26	21	10	17	20	91

- Part number specification

**KRMS-32-M5-20**

