


MOR-K Flexible Coupling - Oldham Type - Set Screw + Key Type

High torque Electrical Insulation High Allowable Misalignment Small Eccentric Reaction Force

MOR-K



Dimensions

Unit : mm

Part Number	A	L	W	E	F	M	Screw Tightening Torque (N·m)
MOR-15K	15	4.4	16	8.2	2.2	M3	0.7
MOR-17K	17	4.9	19.7	8.2	2.5	M3	0.7
MOR-20K	20	5.8	21.6	12.2	2.9	M3	0.7
MOR-26K	26	7.3	25.6	14.2	3.7	M4	1.7
MOR-30K	30	10	32.6	16.2	5	M4	1.7
MOR-34K	34	11.1	34	16.2	5.6	M5	4
MOR-38K	38	12.1	40.1	20.3	6.1	M5	4
MOR-45K	45	13.8	46	22.3	6.9	M6	7
MOR-55K	55	18.7	57	26.5	9.4	M8	15
MOR-68K	68	24	77	38.5	12	M10	30

Unit : mm

Part Number	Standard Metric Bore Diameter (dimensional allowance H8)															
	D1・D2 2															
	6	8	10	12	14	15	16	18	20	22	25	28	30	35	38	
MOR-15K	●	●														
MOR-17K	●	●														
MOR-20K	●	●	●													
MOR-26K	●	●	●	●	●											
MOR-30K		●	●	●	●	●	●									
MOR-34K			●	●	●	●	●									
MOR-38K			●	●	●	●	●	●	●							
MOR-45K			●	●	●	●	●	●	●	●						
MOR-55K					●	●	●	●	●	●	●					
MOR-68K								●	●	●	●	●	●	●	●	

Unit : inch

Part Number	Standard Inch Bore Diameter (dimensional allowance H7)			
	D1・D2 			
	1 / 2	5 / 8	3 / 4	7 / 8
MOR-26K	●			
MOR-30K	●	●		
MOR-34K	●	●		
MOR-38K	●	●	●	
MOR-45K	●	●	●	
MOR-55K		●	●	●

- All products are provided with hex socket set screws.
- Recommended tolerance for shaft diameters is h6 and h7.
- A set of hubs with key type for one side and clamping type for the other side is available upon request.
- For the shaft insertion amount to the coupling, see Mounting/maintenance.

Additional Keyway at Shaft Hole → P.0000 Cleanroom Wash & Packaging → P.0000 Change to Stainless Steel Screw → P.0000

Please feel free to contact us Please feel free to contact us Available / Add'l charge


Performance

Part Number	Max. Bore Diameter (mm)	Rated Torque *1 (N·m)	Maximum Torque *1 (N·m)	Max. Rotational Frequency (min ⁻¹)	Moment *2 of Inertia (kg·m ²)	Static Torsional Stiffness (N·m/rad)	Max. Lateral Misalignment (mm)	Max. Angular Misalignment (°)	Mass *2 (g)
MOR-15K	8	1.6	3.2	42000	1.4×10 ⁻⁷	80	1	3	4
MOR-17K	8	2.2	4.4	37000	2.8×10 ⁻⁷	120	1.2	3	7
MOR-20K	12	3.2	6.4	31000	5.6×10 ⁻⁷	120	1.2	3	8
MOR-26K	14	6	12	24000	2.0×10 ⁻⁶	300	1.5	3	19
MOR-30K	16	15	30	21000	5.4×10 ⁻⁶	530	2	3	37
MOR-34K	16	16	32	18000	9.0×10 ⁻⁶	1000	2.5	3	51
MOR-38K	20	28	56	16000	1.5×10 ⁻⁵	1500	2.5	3	68
MOR-45K	22	30	60	14000	3.2×10 ⁻⁵	2400	3	3	110
MOR-55K	26	45	90	11000	1.0×10 ⁻⁴	4100	4	3	230
MOR-68K	38	80	160	9000	3.3×10 ⁻⁴	6400	4.5	3	430

*1 : Values with no load fluctuation and rotation in a single direction. If there is large load fluctuation, or both normal and reverse rotation, select a size with some margin. If ambient temperature exceeds 30°C, be sure to correct the rated torque and max. torque with temperature correction factor shown in the following table. The allowable operating temperature of **MOR-K** is -20°C to 80°C.

*2 : These are values with max. bore diameter.

Details of Shaft Hole



Metric Shaft Hole

Unit : mm

Standard Bore Diameter D	Keyway				Key Nominal Dimension b x h
	b	t	Standard Dimension	Allowance (JS9)	
6	2	±0.0125	1.0	+0.1 0	2 × 2
8	3	±0.0125	1.4	+0.1 0	3 × 3
10・12	4	±0.0150	1.8	+0.1 0	4 × 4
14・15・16	5	±0.0150	2.3	+0.1 0	5 × 5
18・20・22	6	±0.0150	2.8	+0.1 0	6 × 6
25・28・30	8	±0.0180	3.3	+0.2 0	8 × 7
35・38	10	±0.0180	3.3	+0.2 0	10 × 8


Excerpt from JIS B 1301

Inch Shaft Hole

Unit : inch

Standard Inch Bore Diameter D	Keyway			
	Wk	T	Standard Dimension	Allowance
1 / 2	1 / 8	0.560	+0.002 0	+0.01 0
5 / 8	3 / 16	0.709	+0.002 0	+0.01 0
3 / 4	3 / 16	0.837	+0.002 0	+0.01 0
7 / 8	3 / 16	0.964	+0.002 0	+0.01 0

Comparison of rated torque



Ambient Temperature / Temperature Correction Factor

Ambient Temperature	Temperature Correction Factor
-20°C to 30°C	1.00
30°C to 40°C	0.80
40°C to 60°C	0.70
60°C to 80°C	0.55

Part number specification

MOR-26K-8-10 1 Set

MOR-20 - **SPCR** Single Spacer

Product Code Outside Diameter (A Dimension) Single Spacer