


SPC-W Plastic Washers - PC

Lightweight Electrical Insulation



- PC (polycarbonate) washers.
- PC (polycarbonate) has the highest shock resistance of engineering plastics.
- Allowable operating temperature*1 (min./max.): -40°C/115°C
- PC has low water absorbency and excellent weather resistance.
- For the properties and precautions for use of plastic screws, see "Properties of Plastic Screws."

● Application

Electrical and electronic equipment

● Material/Finish



SPC-W	
Main Body	PC (Polycarbonate) (Transparent)
Heat Resistance Temperature*1	115°C

*1: This is the value for the resin material. The operating temperature of the product changes with performance conditions such as tightening torque.



Unit : mm

Part Number	d	D	t	Nominal	Mass (g)	Qty per Pack
SPC-2-W	2.1	4	0.5	2	0.0055	100
SPC-2-W(1000)	2.1	4	0.5	2	0.0055	1000
SPC-2.6-W	2.7	6	0.5	2.6	0.01	100
SPC-2.6-W(1000)	2.7	6	0.5	2.6	0.01	1000
SPC-3-W	3.3	8	0.8	3	0.04	100
SPC-3-W(1000)	3.3	8	0.8	3	0.04	1000
SPC-3L-W	3.3	10	0.8	3	0.067	100
SPC-3L-W(1000)	3.3	10	0.8	3	0.067	1000
SPC-4-W	4.5	10	0.8	4	0.06	100
SPC-4-W(1000)	4.5	10	0.8	4	0.06	1000
SPC-5-W	5.5	12	0.8	5	0.086	100
SPC-5-W(1000)	5.5	12	0.8	5	0.086	1000
SPC-6-W	6.5	13	1	6	0.12	50
SPC-6-W(1000)	6.5	13	1	6	0.12	1000
SPC-8-W	8.5	18	1.6	8	0.33	50
SPC-8-W(500)	8.5	18	1.6	8	0.33	500
SPC-10-W	10.5	22	1.6	10	0.56	20
SPC-10-W(500)	10.5	22	1.6	10	0.56	500
SPC-12-W	13	24	2.5	12	0.96	20
SPC-12-W(500)	13	24	2.5	12	0.96	500

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part Number Specification

SPC-4-W



Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Not Available	Not Available	Not Available