







KRM | KRMS Male Screw

Part Number Steel	Part Number Stainless steel	D	M (Coarse)	Lm	H	s	d	Mass (g)
KRM-25-M4-6		25	M4	6	19	8	13	6
KRM-25-M4-10		25	M4	10	19	8	13	7
KRM-25-M4-16		25	M4	16	19	8	13	7
KRM-32-M5-10	KRMS-32-M5-10	32	M5	10	22	10	15	11
KRM-32-M5-16	KRMS-32-M5-16	32	M5	16	22	10	15	12
KRM-32-M5-20	KRMS-32-M5-20	32	M5	20	22	10	15	12
KRM-32-M6-10		32	M6	10	22	10	15	12
KRM-32-M6-20		32	M6	20	22	10	15	14
KRM-32-M6-40		32	M6	40	22	10	15	19
KRM-40-M6-10	KRMS-40-M6-10	40	M6	10	25	11	17	16
KRM-40-M6-16	KRMS-40-M6-16	40	M6	16	25	11	17	18
KRM-40-M6-20	KRMS-40-M6-20	40	M6	20	25	11	17	18
KRM-40-M6-25	KRMS-40-M6-25	40	M6	25	25	11	17	19
KRM-40-M8-16		40	M8	16	25	11	17	23
KRM-40-M8-20		40	M8	20	25	11	17	25
KRM-50-M8-16	KRMS-50-M8-16	50	M8	16	30	13.5	20	29
KRM-50-M8-20	KRMS-50-M8-20	50	M8	20	30	13.5	20	31
KRM-50-M8-25	KRMS-50-M8-25	50	M8	25	30	13.5	20	33
KRM-50-M8-30	KRMS-50-M8-30	50	M8	30	30	13.5	20	35
KRM-50-M8-50		50	M8	50	30	13.5	20	43
KRM-50-M10-20		50	M10	20	30	13.5	20	40
KRM-50-M10-30		50	M10	30	30	13.5	20	46
KRM-63-M10-20		63	M10	20	35	15	23	55
KRM-63-M10-30	KRMS-63-M10-30	63	M10	30	35	15	23	61
KRM-63-M10-50	KRMS-63-M10-50	63	M10	50	35	15	23	73

Unit : mm



- Three types: Male Screw **KRM** **KRMS** / Female Screw **KRF** **KRFS** / Reamer Bore **KRR**.
- The reamer hole **KRR** hub has a guide hole for the fixing pin.
- A rich variety of thread sizes from M4 to M10 are available.
- Types and thread part materials can be selected by a product code.

Product Code	Type	Thread Part Material
KRM	Male Screw	Made of Steel
KRMS	Male Screw	Made of Stainless Steel
KRF	Female Screw	Made of Steel
KRFS	Female Screw	Made of Stainless Steel
KRR	Reamer Bore	Made of Steel

• Material/Finish

RoHS2 Compliant

	KRM	KRMS	KRF	KRFS	KRR
knob	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)	Nylon 6 (Matte Black)
Thread Part	SWCH10R Trivalent Chromate Treatment	SUSXM7	SUM24L Trivalent chromate treatment	SUS303	
Hub					SS400 Ferrosferric Oxide Film (Black)

KRF | KRFS Female Screw

Part Number Steel	Part Number Stainless steel	D	M (Coarse)	Lf	H	s	d	Mass (g)
KRF-25-M4		25	M4	8	19	8	13	13
KRF-32-M5	KRFS-32-M5	32	M5	10	22	10	15	15
KRF-32-M6		32	M6	10	22	10	15	15
KRF-40-M6	KRFS-40-M6	40	M6	15	25	11	17	17
KRF-40-M8		40	M8	15	25	11	17	15
KRF-50-M8	KRFS-50-M8	50	M8	18	30	13.5	20	27
KRF-50-M10		50	M10	20	30	13.5	20	24
KRF-63-M10	KRFS-63-M10	63	M10	20	35	15	23	55

Unit : mm

KRR Reamer Bore

Part Number Steel	D	C	Lc	H	C1	d2	d	f	h	s	Mass (g)
KRR-40-R8	40	8	15	25	2.8	19	14	7	9	11	27
KRR-50-R10	50	10	19	32	2.8	22	17	8	13	15.5	47
KRR-63-R12	63	12	23	40	3.8	26	21	10	17	20	91

Unit : mm

• Part number specification

KRMS-32-M5-20

1