



- Thermosetting resin. It has a high durability.
- Types can be selected by a product code. **1**
  - PB** — Without insert
  - PC** — With insert
- There are two color variations. They can be selected by the end symbol of the part number. **4**
  - End Symbol **BK** — Black
  - End Symbol **RD** — Red

• Material/Finish

RoHS2 Compliant

	<b>PB</b>	<b>PC</b>
Ball Part	<b>BK</b> : Phenol Resin (Black) <b>RD</b> : Melamine Resin (Red)	<b>BK</b> : Phenol Resin (Black) <b>RD</b> : Melamine Resin (Red)
Thread Part		Brass

**PB** Without Insert **PC** With Insert

Unit : mm

Part Number	D <b>2</b>	M (Coarse) <b>3</b>	Lf	H	Mass (g)
<b>PB-20-M6</b>	20	M6	10	18	5.6
<b>PB-20-M8</b>	20	M8	10	18	5.2
<b>PB-25-M6</b>	25	M6	10	23	11
<b>PB-25-M8</b>	25	M8	12	23	10
<b>PB-30-M8</b>	30	M8	16	28	19
<b>PB-30-M10</b>	30	M10	18	28	18
<b>PB-35-M8</b>	35	M8	16	32	31
<b>PB-35-M10</b>	35	M10	18	32	30
<b>PB-40-M10</b>	40	M10	18	37	47
<b>PB-40-M12</b>	40	M12	18	37	44
<b>PC-20-M6</b>	20	M6	10	18	7
<b>PC-25-M6</b>	25	M6	10	23	15
<b>PC-25-M8</b>	25	M8	12	23	15
<b>PC-30-M8</b>	30	M8	12	28	30
<b>PC-30-M10</b>	30	M10	15	28	30
<b>PC-35-M8</b>	35	M8	12	32	40
<b>PC-35-M10</b>	35	M10	15	32	40
<b>PC-40-M10</b>	40	M10	15	37	55
<b>PC-40-M12</b>	40	M12	15	37	50

• Part number specification



Cleanroom Wash & Packaging → P.xxxx	Screw Combination → P.xxxx	Screw Length Adjustment → P.xxxx	Vibration Resistant → P.xxxx	Laser Marking → P.xxxx
Available / Add'l charge	Not Available	Not Available	Not Available	<b>BK</b> only/ Add'l charge