




# SWUT Hex Lock Nuts - Titanium

Cleanroom wash & packaging
 Non-Magnetic
 Lightweight
 Vibration resistant treatment



- Specific gravity is approximately 60% of stainless steel.
- These nuts are equipped with vibration resistant patch to prevent screw from loosening.
- Continuous Max. Operating Temperature :  
-40 to 120 deg C

### ● Application

Lightweight applications in automobiles, aircrafts, spacecrafts, and robots FPD production equipment, semiconductor devices, electrical and electronic equipment, and loosening prevention

### ● Material/Finish



	SWUT
Main Body	FRS-9901 (Equivalent to TW340)
Nylon Ring	Nylon 66

Unit : mm

Part Number	M (Coarse)		B	C(Approx.)	T	Mass (g)
	Nominal of Thread	Pitch				
<b>SWUT-M3</b>	M3	0.5	5.5	6.4	4	0.27
<b>SWUT-M4</b>	M4	0.7	7	8.1	5	0.52
<b>SWUT-M5</b>	M5	0.8	8	9.2	6.5	0.77
<b>SWUT-M6</b>	M6	1	10	11.5	8	1.8
<b>SWUT-M8</b>	M8	1.25	13	15	9.8	3.5
<b>SWUT-M10</b>	M10	1.5	17	19.6	12	7.3

### ● Part number specification

## SWUT-M6



Batch cleanroom packing is provided for orders containing multiple items of the same size.

Individual Sales → P.0000	Cleanroom Wash & Packaging → P.0000	Screw Length Adjustment → P.0000	Vibration Resistant → P.0000	Modification process for captive use → P.0000
1 piece in 1 pack	Cleanroom washed and packed	Not Available	Not Available	Not Available