

Thickness: approximately 0.3 mm

- **FSS-V** (Background color: Silver) Multiples of 0 and 50 are red.
- **FSS-V-BK** (Background color: Black) All numbers are silver.

- Sticker type vertical scale. Use by sticking to machinery and equipment.
- Standardized 100/200/300/500 mm scale length.
- Made of flexible polyester. Can be stuck to the curved surfaces of posts or shafts, plus can be cut to a desired length for use.
- Corners are rounded. Doesn't come off easily.
- There are 3 types of scales. They can be selected by the symbol of the part number.

Symbol	Scale
<b>T</b>	Zero Point at the Bottom
<b>B</b>	Zero Point at the Top
<b>C</b>	Center Distribution

- There are two color variations available. They can be selected by the end symbol of the part number.

End Symbol	Background Color	Scale / Numbers
<b>No</b>	Silver	Red/Black
<b>BK</b>	Black	Silver

- Material/Finish



	<b>FSS-V</b>
Main Body	Polyester Aluminum Evaporation Coating

**FSS-V** Background color: Silver **FSS-V-BK** Background color: Black

Unit : mm


Part Number	L1	L	Mass (g)
FSS-100V-T	100	108	0.5
FSS-200V-T	200	208	1
FSS-300V-T	300	308	1.5
FSS-500V-T	500	508	2.5
FSS-100V-B	100	108	0.5
FSS-200V-B	200	208	1
FSS-300V-B	300	308	1.5
FSS-500V-B	500	508	2.5
FSS-100V-C	100	108	0.5
FSS-200V-C	200	208	1
FSS-300V-C	300	308	1.5
FSS-500V-C	500	508	2.5
FSS-100V-T-BK	100	108	0.5
FSS-200V-T-BK	200	208	1
FSS-300V-T-BK	300	308	1.5
FSS-500V-T-BK	500	508	2.5
FSS-100V-B-BK	100	108	0.5
FSS-200V-B-BK	200	208	1
FSS-300V-B-BK	300	308	1.5
FSS-500V-B-BK	500	508	2.5
FSS-100V-C-BK	100	108	0.5
FSS-200V-C-BK	200	208	1
FSS-300V-C-BK	300	308	1.5
FSS-500V-C-BK	500	508	2.5

Scale Plate / Scale sticker Length Adjustment → P.xxxx

Available / Add'l charge

### ⚠ Precautions for Use

- Use the scale of the **FSS-V** Scale Sticker as a general guideline.
- Thoroughly remove oil and dust on the sticking surface before sticking.



### • Related Products

Point Lens **FLE**, which is useful to read the scale, is available.



- Part number specification

**FSS-200V-T-BK**

