

- Procedure of Selection
- (1) Select either type A or type B, based on the crosssection shape of the T-slot in the aluminum frame.
- ②Select a part number where W and T₁ match with the dimensions of the T-slot in the aluminum frame.
- (3) Confirm that the dimensions of the T-slot in the aluminum frame are T2 or higher.



- Bracket for simple positioning when using the T-slot in a vertical axis aluminum frame.
- \bullet Can be mounted to \square 20 to \square 80 aluminum frames. For details, refer to Selection Method.
- Push the push button to unlock the lock, smoothly move the bracket vertically, and release the push button to fix it in position.
- It can be moved upward without pushing the push button, just by applying force.
- Load capacity of up to 5 kg.
- Push button press count resistance is 20,000 times (reference value).


A POHC

Material/Finish

		₩ KONS				
		CUTB-L				
Bracket Body		A6063 Electrostatic Coating (metallic silver)				
Cover		Aluminum Die Cast Electrostatic Coating (metallic silver)				
Push Button		Polyacetal (Black)				
Nut		Steel				
Spacer		Steel				
Grub Screw	Thread Part	Chromium-molybdenum Steel Ferrosoferric Oxide Film (Black)				
	Pad	Polyacetal (White)				

										Unit:mm
Part Number 1	Nut/Frame Type	W 1	W2	t1	t ₂	Aluminur T1		W	Max. Load Weight (kg)	Mass (g)
CUTB-60-190-A1-L	Α	5.8	10	3.6	3.3	2	4	6	5	347
CUTB-60-190-A2-L	A	7.8	15	3.6	5.5	2	7	8	5	366
CUTB-60-190-A3-L	Α	9.8	17	7	6	5.5	7	10	5	385
CUTB-60-190-A4-L	Α	9.8	17	7.5	6	6	7	10	5	385
CUTB-60-190-B1-L	В	5.3	10	4	5	2.5	5.5	6.3	5	351
CUTB-60-190-B2-L	В	5.3	13.7	5.5	6.5	4	7	8.3	5	356





 Push the CUTB-L button, and insert onto the T-slot in the aluminum frame in the unlocked state.

*1: Mounting bolts are not supplied.

• **CUTB-L** requires vertical mounting. If mounted

• Mounting to the aluminum frame with the

upside-down, **CUTB-L** cannot remain fixed onto

workpiece mounted onto **CUTB-L** may prevent

the aluminum frame from being fixed in position.

Follow the mounting procedure when mounting

• **CUTB-L** is a product that uses friction fastening. In

frame causes the friction coefficient to decrease or

if impact loads or vibrations occur, the maximum

• When pressing the push button on **CUTB-L** to move the workpiece, make sure to support **CUTB-L** or the workpiece with both hands. Pressing the push button may cause a sudden

drop, especially if a heavy object is loaded. • The surface may be scratched depending on the material and surface finish of the aluminum frame. • If excessive loads are applied, then the aluminum frame may be scratched or **CUTB-L** may be

• Pressing the push button while wearing gloves could cause the glove material to get caught

between the push button and bracket body. This may prevent the push button from being released,

which will prevent the aluminum frame from being

cases where oil, etc. adhered to the aluminum

Precautions for Use

aluminum frames.

the workpiece.


load weight may decrease.

Mount to a vertical axis.


- 2 Release the **3** Lightly push push button to fix **CUTB-L** in place.
 - the two grub screws to the aluminum frame with the hexagon key.

Grub screw

(Sold separately) **4** Loosen the **6** Mount the two grub screws pushed to the aluminum



- workpiece button again with **CUTB-L** enables **CUTB-L** fixed in place. to be moved to frame 90°±15°. the desired position.
- The grub screw adjusted in steps 3 and 4 in the mounting procedure is used to prevent **CUTB-L** from being tilted with respect to the aluminum frame. If **CUTB-L** is tilted, it could prevent the aluminum frame from being held properly in position. Make sure to follow the mounting procedure when mounting **CUTB-L**.
- If the grub screw is loose or worn, it could prevent **CUTB-L** from fixing the aluminum frame into position. Make sure to follow steps 3 and 4 in the mounting procedure.



- Take care to pay attention to the vertical orientation when mounting.
- Part number specification

CUTB-60-190-A3-L

NBK. ▶ https://www.nbk1560.com fixed in position.

damaged.